

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298340

Luminaire Tested: P3A13R60W2N902765DE010 E3CB1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298340
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902765DE010 E3CB1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 896.1 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298340

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1298340

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97	96	95		94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89		87
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88	85	83		81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77		76
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79	75	72		71
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74	70	68		66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63		62
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67	62	59		58
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63	59	56		55
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60	56	53		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213952
5°	205480
10°	211553
15°	214280
20°	189203
25°	159445
30°	129311
35°	84216
40°	38672
45°	14823
50°	4981
55°	1338
60°	1228
65°	1090
70°	898
75°	1186
80°	884
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14823 cd/sqm

TEST NUMBER: P1298340

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.8	10.0
10°-20°	258.5	28.8
20°-30°	301.5	33.6
30°-40°	194.5	21.7
40°-50°	43.6	4.9
50°-60°	4.4	0.5
60°-70°	2.1	0.2
70°-80°	1.2	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	649.8	72.5
0°-40°	844.3	94.2
0°-60°	892.3	99.6
0°-90°	896.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	896.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	976	
5°	934	90
15°	944	258
25°	659	301
35°	315	195
45°	48	44
55°	4	4
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1298340

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	975.7
2.5°	959.8
5°	933.5
7.5°	932.1
10°	950.1
12.5°	961.9
15°	943.9
17.5°	889.8
20°	810.8
22.5°	728.3
25°	659.0
27.5°	591.1
30°	510.7
32.5°	416.5
35°	314.6
37.5°	214.8
40°	135.1
42.5°	81.1
45°	47.8
47.5°	27.7
50°	14.6
52.5°	4.9
55°	3.5
57.5°	2.8
60°	2.8
62.5°	2.1
65°	2.1
67.5°	2.1
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)