

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298347

Luminaire Tested: P3A13R60W2N902765DE010 E3CB1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902765DE010 E3CB1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 988.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298347

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298347

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97	96	95		94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89		87
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88	85	83		81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77		76
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79	75	72		71
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74	70	68		66
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70	66	63		62
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67	62	59		58
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63	59	56		55
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60	56	53		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	235924
5°	226568
10°	233262
15°	236278
20°	208641
25°	175825
30°	142604
35°	92862
40°	42651
45°	16343
50°	5458
55°	1453
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 16343 cd/sqm

TEST NUMBER: P1298347

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.1	10.0
10°-20°	285.0	28.8
20°-30°	332.4	33.6
30°-40°	214.5	21.7
40°-50°	48.1	4.9
50°-60°	4.8	0.5
60°-70°	2.3	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	716.5	72.5
0°-40°	931.0	94.2
0°-60°	983.9	99.6
0°-90°	988.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	988.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1076	
5°	1029	99
15°	1041	285
25°	727	332
35°	347	215
45°	53	48
55°	4	5
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1298347

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1075.9
2.5°	1058.3
5°	1029.3
7.5°	1027.8
10°	1047.6
12.5°	1060.6
15°	1040.8
17.5°	981.2
20°	894.1
22.5°	803.1
25°	726.7
27.5°	651.8
30°	563.2
32.5°	459.3
35°	346.9
37.5°	236.9
40°	149.0
42.5°	89.4
45°	52.7
47.5°	30.6
50°	16.0
52.5°	5.3
55°	3.8
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	2.3
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)