

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298395

Luminaire Tested: P3A13R60W2N902765DE010 E3D1WMH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902765DE010 E3D1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 916.0 lumens
Efficiency: N/A
Efficacy: 74.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298395
CATALOG NUMBER: P3A13R60W2N902765DE010 E3D1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298395

CATALOG NUMBER: P3A13R60W2N902765DE010 E3D1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240003
5°	226568
10°	220682
15°	215643
20°	200497
25°	179236
30°	136907
35°	79050
40°	30686
45°	12777
50°	2797
55°	421
60°	307
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12777 cd/sqm



TEST NUMBER: P1298395

CATALOG NUMBER: P3A13R60W2N902765DE010 E3D1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.2	10.6
10°-20°	264.6	28.9
20°-30°	331.4	36.2
30°-40°	185.3	20.2
40°-50°	35.2	3.8
50°-60°	1.8	0.2
60°-70°	0.4	0.0
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.2	75.7
0°-40°	878.4	95.9
0°-60°	915.4	99.9
0°-90°	916.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	916.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1094	
5°	1029	97
15°	950	265
25°	741	331
35°	295	185
45°	41	35
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1298395

CATALOG NUMBER: P3A13R60W2N902765DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1094.5
1°	1090.0
2°	1075.8
3°	1058.9
4°	1043.2
5°	1029.3
6°	1018.8
7°	1009.8
8°	1003.1
9°	996.7
10°	991.1
11°	985.5
12°	979.1
13°	971.2
14°	961.9
15°	949.9
16°	935.3
17°	918.8
18°	900.0
19°	878.7
20°	859.2
21°	838.2
22°	816.5
23°	793.6
24°	768.5
25°	740.8
26°	708.2
27°	671.8
28°	631.0
29°	587.5
30°	540.7
31°	493.5
32°	444.8
32.5°	418.2
33°	394.2
34°	344.4
35°	295.3
36°	251.1
37°	204.2
37.5°	182.9
38°	161.9
39°	130.4
40°	107.2
42.5°	65.2
45°	41.2



TEST NUMBER: P1298395
CATALOG NUMBER: P3A13R60W2N902765DE010 E3D1WMH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	22.9
50°	8.2
52.5°	1.9
55°	1.1
57.5°	0.7
60°	0.7
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)