

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298404

Luminaire Tested: P3A13R60W2N902765DE010 E3DL1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902765DE010 E3DL1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 398.0 lumens
Efficiency: N/A
Efficacy: 32.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298404

CATALOG NUMBER: P3A13R60W2N902765DE010 E3DL1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298404

CATALOG NUMBER: P3A13R60W2N902765DE010 E3DL1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93984
5°	93088
10°	90379
15°	84677
20°	74953
25°	62689
30°	49147
35°	35657
40°	23702
45°	14792
50°	8017
55°	2332
60°	2149
65°	1972
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14792 cd/sqm

TEST NUMBER: P1298404

CATALOG NUMBER: P3A13R60W2N902765DE010 E3DL1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	10.0
10°-20°	103.5	26.0
20°-30°	118.0	29.6
30°-40°	83.6	21.0
40°-50°	38.0	9.5
50°-60°	8.1	2.0
60°-70°	3.9	1.0
70°-80°	2.4	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.3	65.6
0°-40°	344.9	86.7
0°-60°	390.9	98.2
0°-90°	398.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	398.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	429	
5°	423	40
15°	373	103
25°	259	118
35°	133	84
45°	48	38
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1298404

CATALOG NUMBER: P3A13R60W2N902765DE010 E3DL1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	428.6
2.5°	427.1
5°	422.9
7.5°	415.7
10°	405.9
12.5°	391.9
15°	373.0
17.5°	349.1
20°	321.2
22.5°	290.9
25°	259.1
27.5°	226.6
30°	194.1
32.5°	163.0
35°	133.2
37.5°	106.7
40°	82.8
42.5°	62.8
45°	47.7
47.5°	35.6
50°	23.5
52.5°	11.0
55°	6.1
57.5°	5.3
60°	4.9
62.5°	4.5
65°	3.8
67.5°	3.4
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)