

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298795

Luminaire Tested: P3A13R65W2N902765DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R65W2N902765DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 262.1 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298795

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298795

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90	88	86		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85	82	79		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80	76	73		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71	66	63		62
7	81	71	65	60	79	70	64	60	69	63	60		68	63	59		67	62	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66596
5°	64935
10°	60475
15°	54189
20°	46811
25°	38930
30°	30714
35°	22754
40°	15687
45°	9737
50°	5288
55°	3326
60°	2807
65°	2542
70°	2180
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9737 cd/sqm

TEST NUMBER: P1298795

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.4	10.5
10°-20°	66.3	25.3
20°-30°	73.4	28.0
30°-40°	53.3	20.3
40°-50°	25.0	9.5
50°-60°	8.4	3.2
60°-70°	4.9	1.9
70°-80°	2.5	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.1	63.8
0°-40°	220.4	84.1
0°-60°	253.8	96.9
0°-90°	262.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	262.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	304	
5°	295	27
15°	239	66
25°	161	73
35°	85	53
45°	31	25
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1298795

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	303.7
2.5°	301.8
5°	295.0
7.5°	284.8
10°	271.6
12.5°	256.1
15°	238.7
17.5°	219.8
20°	200.6
22.5°	180.6
25°	160.9
27.5°	140.9
30°	121.3
32.5°	102.4
35°	85.0
37.5°	69.1
40°	54.8
42.5°	41.9
45°	31.4
47.5°	22.7
50°	15.5
52.5°	10.6
55°	8.7
57.5°	7.6
60°	6.4
62.5°	5.7
65°	4.9
67.5°	4.2
70°	3.4
72.5°	3.0
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)