

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298806

Luminaire Tested: P3A13R65W2N902765DE010 E3DLP1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R65W2N902765DE010 E3DLP1LI_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 43.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298806

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1LI_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298806

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1LI_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136743
5°	133348
10°	124179
15°	111283
20°	96118
25°	79940
30°	63048
35°	46712
40°	32203
45°	19971
50°	10848
55°	6805
60°	5789
65°	5241
70°	4488
75°	3982
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19971 cd/sqm

TEST NUMBER: P1298806

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	10.5
10°-20°	136.2	25.3
20°-30°	150.6	28.0
30°-40°	109.4	20.3
40°-50°	51.3	9.5
50°-60°	17.2	3.2
60°-70°	10.0	1.9
70°-80°	5.2	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.2	63.8
0°-40°	452.6	84.1
0°-60°	521.1	96.9
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	624	
5°	606	56
15°	490	136
25°	330	151
35°	174	109
45°	64	51
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1298806

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLP1LI_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	623.6
2.5°	619.8
5°	605.8
7.5°	584.8
10°	557.7
12.5°	525.9
15°	490.2
17.5°	451.4
20°	411.9
22.5°	370.8
25°	330.4
27.5°	289.3
30°	249.0
32.5°	210.2
35°	174.5
37.5°	141.9
40°	112.5
42.5°	86.1
45°	64.4
47.5°	46.5
50°	31.8
52.5°	21.7
55°	17.8
57.5°	15.5
60°	13.2
62.5°	11.6
65°	10.1
67.5°	8.5
70°	7.0
72.5°	6.2
75°	4.7
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)