

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298858

Luminaire Tested: P3A13R70W2N902750DE010 E3D1H_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298858
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R70W2N902750DE010 E3D1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 912.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298858
CATALOG NUMBER: P3A13R70W2N902750DE010 E3D1H_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298858
 CATALOG NUMBER: P3A13R70W2N902750DE010 E3D1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177332
5°	167202
10°	158559
15°	155688
20°	150070
25°	141468
30°	140452
35°	122335
40°	79120
45°	37399
50°	5254
55°	421
60°	307
65°	363
70°	256
75°	339
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37399 cd/sqm



TEST NUMBER: P1298858

CATALOG NUMBER: P3A13R70W2N902750DE010 E3D1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.9	7.8
10°-20°	192.6	21.1
20°-30°	272.5	29.9
30°-40°	273.8	30.0
40°-50°	98.5	10.8
50°-60°	2.6	0.3
60°-70°	0.6	0.1
70°-80°	0.4	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.0	58.8
0°-40°	809.8	88.8
0°-60°	910.9	99.9
0°-90°	912.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	912.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	809	
5°	760	71
15°	686	193
25°	585	272
35°	457	274
45°	121	98
55°	1	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1298858
CATALOG NUMBER: P3A13R70W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	808.7
1°	806.5
2°	799.3
3°	788.1
4°	773.9
5°	759.6
6°	746.1
7°	735.7
8°	726.3
9°	718.8
10°	712.1
11°	706.4
12°	701.2
13°	696.0
14°	691.1
15°	685.8
16°	679.5
17°	672.7
18°	664.5
19°	654.4
20°	643.1
21°	630.8
22°	618.4
23°	606.4
24°	594.8
25°	584.7
26°	577.6
27°	572.0
28°	567.5
29°	562.2
30°	554.7
31°	543.9
32°	528.5
32.5°	519.9
33°	508.3
34°	485.4
35°	457.0
36°	425.5
37°	389.9
37.5°	373.4
38°	351.0
39°	310.9
40°	276.4
42.5°	191.4
45°	120.6



TEST NUMBER: P1298858
CATALOG NUMBER: P3A13R70W2N902750DE010 E3D1H_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	64.8
50°	15.4
52.5°	1.9
55°	1.1
57.5°	1.1
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)