

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296600

Luminaire Tested: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296600
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R30W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 19.8 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296600

CATALOG NUMBER: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot



TEST NUMBER: P1296600

CATALOG NUMBER: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87	84	82	80
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82	79	76	74
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78	74	71	70
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74	70	67	65
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70	66	63	61
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67	62	59	58
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60	56	53	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83371
5°	80783
10°	72789
15°	60205
20°	46624
25°	34962
30°	25396
35°	16918
40°	10391
45°	6109
50°	3753
55°	3020
60°	2675
65°	2179
70°	1923
75°	1949
80°	1389
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6109 cd/sqm

TEST NUMBER: P1296600

CATALOG NUMBER: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.8	13.8
10°-20°	73.0	29.9
20°-30°	66.5	27.2
30°-40°	40.2	16.5
40°-50°	16.1	6.6
50°-60°	7.1	2.9
60°-70°	4.3	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	71.0
0°-40°	213.4	87.5
0°-60°	236.7	97.0
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	380	
5°	367	34
15°	265	73
25°	144	66
35°	63	40
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1296600

CATALOG NUMBER: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	380.2
1°	379.9
2°	378.3
3°	375.7
4°	371.9
5°	367.0
6°	360.9
7°	354.5
8°	346.2
9°	336.7
10°	326.9
11°	315.5
12°	303.4
13°	291.3
14°	278.1
15°	265.2
17.5°	231.5
20°	199.8
22.5°	170.3
25°	144.5
27.5°	121.1
30°	100.3
32.5°	81.0
35°	63.2
37.5°	48.4
40°	36.3
42.5°	26.5
45°	19.7
47.5°	14.8
50°	11.0
52.5°	8.7
55°	7.9
57.5°	6.8
60°	6.1
62.5°	4.9
65°	4.2
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.1
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1296600

CATALOG NUMBER: P3A13R30W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)