

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299213

Luminaire Tested: P3A17R15W2N902750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R15W2N902750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 942.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299213

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1299213

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237613
5°	231168
10°	211241
15°	185041
20°	158727
25°	132540
30°	106067
35°	79531
40°	57737
45°	37740
50°	23607
55°	15980
60°	14122
65°	13023
70°	12246
75°	11099
80°	10607
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 37740 cd/sqm

TEST NUMBER: P1299213

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.9	10.3
10°-20°	227.1	24.1
20°-30°	250.2	26.6
30°-40°	187.4	19.9
40°-50°	97.1	10.3
50°-60°	40.3	4.3
60°-70°	24.9	2.6
70°-80°	14.0	1.5
80°-90°	4.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.2	61.0
0°-40°	761.6	80.8
0°-60°	899.0	95.4
0°-90°	942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1050	97
15°	815	227
25°	548	250
35°	297	187
45°	122	97
55°	42	40
65°	25	25
75°	13	14
85°	4	4
90°	0	

TEST NUMBER: P1299213

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1083.6
1°	1084.8
2°	1081.2
3°	1074.0
4°	1063.3
5°	1050.2
6°	1033.5
7°	1015.6
8°	994.1
9°	971.4
10°	948.7
12.5°	883.1
15°	815.1
17.5°	747.0
20°	680.2
22.5°	612.2
25°	547.8
27.5°	483.3
30°	418.9
32.5°	355.6
35°	297.1
37.5°	247.0
40°	201.7
42.5°	159.9
45°	121.7
47.5°	91.9
50°	69.2
52.5°	51.3
55°	41.8
57.5°	37.0
60°	32.2
62.5°	28.6
65°	25.1
67.5°	21.5
70°	19.1
72.5°	15.5
75°	13.1
77.5°	10.7
80°	8.4
82.5°	6.0
85°	3.6
87.5°	1.2
90°	0.0

(END OF REPORT)