

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299330

Luminaire Tested: P3A17R15W2N902765DE010 E3DL1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R15W2N902765DE010 E3DL1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 617.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299330

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1299330

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97		95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93		91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88		87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85		83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81		80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78		77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75		74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73		72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70		69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	527085
5°	467861
10°	324910
15°	192146
20°	109443
25°	62568
30°	34613
35°	18444
40°	10219
45°	5520
50°	3446
55°	2714
60°	2324
65°	2179
70°	1923
75°	2033
80°	1515
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5520 cd/sqm

TEST NUMBER: P1299330

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	29.3
10°-20°	238.5	38.7
20°-30°	122.8	19.9
30°-40°	46.1	7.5
40°-50°	15.1	2.4
50°-60°	6.5	1.0
60°-70°	4.1	0.7
70°-80°	2.5	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.1	87.9
0°-40°	588.2	95.3
0°-60°	609.8	98.8
0°-90°	617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2404	
5°	2126	181
15°	846	239
25°	259	123
35°	69	46
45°	18	15
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1299330

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2403.7
1°	2398.9
2°	2367.4
3°	2307.4
4°	2228.3
5°	2125.5
6°	2009.0
7°	1881.2
8°	1739.2
9°	1598.9
10°	1459.2
12.5°	1122.8
15°	846.4
17.5°	633.6
20°	469.0
22.5°	350.1
25°	258.6
27.5°	188.4
30°	136.7
32.5°	96.9
35°	68.9
37.5°	49.3
40°	35.7
42.5°	25.6
45°	17.8
47.5°	13.1
50°	10.1
52.5°	8.3
55°	7.1
57.5°	5.9
60°	5.3
62.5°	4.8
65°	4.2
67.5°	3.6
70°	3.0
72.5°	3.0
75°	2.4
77.5°	1.8
80°	1.2
82.5°	1.2
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)