

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299347

Luminaire Tested: P3A17R15W2N902765DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299347
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R15W2N902765DE010 E3DL1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1239.0 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299347

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1299347

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97		95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93		91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88		87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85		83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81		80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78		77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75		74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73		72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70		69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1058424
5°	939509
10°	652448
15°	385859
20°	219749
25°	125620
30°	69504
35°	37075
40°	20496
45°	11102
50°	6925
55°	5467
60°	4693
65°	4358
70°	3847
75°	4067
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11102 cd/sqm

TEST NUMBER: P1299347

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	363.0	29.3
10°-20°	479.0	38.7
20°-30°	246.6	19.9
30°-40°	92.6	7.5
40°-50°	30.3	2.4
50°-60°	13.0	1.1
60°-70°	8.3	0.7
70°-80°	4.9	0.4
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.6	87.9
0°-40°	1181.2	95.3
0°-60°	1224.6	98.8
0°-90°	1239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1239.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4827	
5°	4268	363
15°	1700	479
25°	519	247
35°	138	93
45°	36	30
55°	14	13
65°	8	8
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1299347

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4826.8
1°	4817.3
2°	4754.0
3°	4633.5
4°	4474.7
5°	4268.2
6°	4034.3
7°	3777.7
8°	3492.4
9°	3210.7
10°	2930.2
12.5°	2254.7
15°	1699.7
17.5°	1272.4
20°	941.7
22.5°	703.0
25°	519.2
27.5°	378.4
30°	274.5
32.5°	194.6
35°	138.5
37.5°	99.1
40°	71.6
42.5°	51.3
45°	35.8
47.5°	26.3
50°	20.3
52.5°	16.7
55°	14.3
57.5°	11.9
60°	10.7
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.0
72.5°	6.0
75°	4.8
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)