

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299437

Luminaire Tested: P3A17R15W2N902765DE010 E3PH1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299437
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R15W2N902765DE010 E3PH1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1020.0 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299437

CATALOG NUMBER: P3A17R15W2N902765DE010 E3PH1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1299437

CATALOG NUMBER: P3A17R15W2N902765DE010 E3PH1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100	100	99	98	97	96	95	94	93	92	91	90	89
2	113	110	108	106	111	109	107	105	106	104	103	103	102	100	100	99	98	97	96	95	94	93	92	91	90	89	88	87	86
3	111	107	104	102	109	106	103	101	104	101	100	101	100	98	99	98	97	96	95	94	93	92	91	90	89	88	87	86	85
4	109	104	101	99	107	103	101	99	102	99	98	100	98	97	98	97	96	95	94	93	92	91	90	89	88	87	86	85	84
5	107	102	99	97	105	101	99	96	100	97	96	99	96	95	97	96	94	93	92	91	90	89	88	87	86	85	84	83	82
6	105	100	97	95	104	100	97	95	98	96	94	97	95	93	96	94	93	92	91	90	89	88	87	86	85	84	83	82	81
7	103	98	95	93	102	98	95	93	97	94	93	96	94	92	95	93	92	91	90	89	88	87	86	85	84	83	82	81	80
8	101	97	94	92	101	96	94	92	96	93	91	95	93	91	94	92	91	90	89	88	87	86	85	84	83	82	81	80	79
9	100	95	92	90	99	95	92	90	94	92	90	94	91	90	93	91	90	89	88	87	86	85	84	83	82	81	80	79	78
10	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	89	88	87	86	85	84	83	82	81	80	79	78	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2150617
5°	1864622
10°	906619
15°	193395
20°	40650
25°	12097
30°	2608
35°	455
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1299437

CATALOG NUMBER: P3A17R15W2N902765DE010 E3PH1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	661.7	64.9
10°-20°	329.0	32.3
20°-30°	27.4	2.7
30°-40°	1.8	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1018.2	99.8
0°-40°	1020.0	100.0
0°-60°	1020.0	100.0
0°-90°	1020.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9808	
5°	8471	662
15°	852	329
25°	50	27
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1299437

CATALOG NUMBER: P3A17R15W2N902765DE010 E3PH1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	9807.6
2.5°	9464.4
5°	8471.0
7.5°	6486.1
10°	4071.7
12.5°	1959.1
15°	851.9
17.5°	434.6
20°	174.2
22.5°	86.2
25°	50.0
27.5°	25.9
30°	10.3
32.5°	3.4
35°	1.7
37.5°	1.7
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)