

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296765

Luminaire Tested: P3A13R35W2N902750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 803.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296765

CATALOG NUMBER: P3A13R35W2N902750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1296765

CATALOG NUMBER: P3A13R35W2N902750DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98	97	96		95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	93	91		90
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91	88	86		85
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87	84	82		80
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83	80	78		76
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80	77	74		73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71		70
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74	70	68		66
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71	68	65		64
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69	65	62		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	404989
5°	389235
10°	339139
15°	259752
20°	173778
25°	105151
30°	60338
35°	33729
40°	17919
45°	9241
50°	4435
55°	3517
60°	3333
65°	2750
70°	2949
75°	2626
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9241 cd/sqm

TEST NUMBER: P1296765

CATALOG NUMBER: P3A13R35W2N902750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	20.0
10°-20°	311.8	38.8
20°-30°	204.1	25.4
30°-40°	82.8	10.3
40°-50°	24.8	3.1
50°-60°	8.4	1.1
60°-70°	5.7	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.8	84.3
0°-40°	759.6	94.6
0°-60°	792.9	98.7
0°-90°	803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1847	
5°	1768	161
15°	1144	312
25°	435	204
35°	126	83
45°	30	25
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296765

CATALOG NUMBER: P3A13R35W2N902750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1846.9
1°	1843.9
2°	1835.5
3°	1818.7
4°	1798.8
5°	1768.3
6°	1730.1
7°	1687.3
8°	1639.2
9°	1584.2
10°	1523.1
11°	1455.1
12°	1384.1
13°	1304.6
14°	1229.0
15°	1144.2
17.5°	938.7
20°	744.7
22.5°	572.9
25°	434.6
27.5°	323.9
30°	238.3
32.5°	174.9
35°	126.0
37.5°	89.4
40°	62.6
42.5°	43.5
45°	29.8
47.5°	19.9
50°	13.0
52.5°	9.9
55°	9.2
57.5°	8.4
60°	7.6
62.5°	6.9
65°	5.3
67.5°	4.6
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1296765

CATALOG NUMBER: P3A13R35W2N902750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)