

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299607

Luminaire Tested: P3A17R20W2N902765DE010 E3CD1MB_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R20W2N902765DE010 E3CD1MB_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 6500K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1522.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299607

CATALOG NUMBER: P3A17R20W2N902765DE010 E3CD1MB_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1299607

CATALOG NUMBER: P3A17R20W2N902765DE010 E3CD1MB_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	116	114	112	110		113	112	110	109		108	106	105		104	103	102		101	100	99		98			
2	112	109	107	104		110	108	105	103		104	103	101		102	100	99		99	98	97		95			
3	109	105	102	100		108	104	101	99		102	99	97		99	98	96		97	96	95		93			
4	107	102	99	96		105	101	98	96		99	97	95		97	95	93		96	94	92		91			
5	104	99	96	93		103	98	95	93		97	94	92		95	93	91		94	92	91		90			
6	102	97	93	91		101	96	93	90		95	92	90		94	91	89		93	90	89		88			
7	100	94	91	88		99	94	91	88		93	90	88		92	89	87		91	89	87		86			
8	98	92	89	86		97	92	89	86		91	88	86		90	88	86		89	87	85		85			
9	96	90	87	85		95	90	87	85		89	86	84		89	86	84		88	86	84		83			
10	94	89	85	83		93	88	85	83		88	85	83		87	84	83		87	84	82		82			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2363846
5°	2051723
10°	1267757
15°	440320
20°	135228
25°	47809
30°	17699
35°	7094
40°	3807
45°	1489
50°	819
55°	918
60°	1053
65°	623
70°	769
75°	1017
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1489 cd/sqm

TEST NUMBER: P1299607

CATALOG NUMBER: P3A17R20W2N902765DE010 E3CD1MB_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	773.6	50.8
10°-20°	613.8	40.3
20°-30°	106.3	7.0
30°-40°	19.3	1.3
40°-50°	4.4	0.3
50°-60°	2.2	0.1
60°-70°	1.3	0.1
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1493.6	98.1
0°-40°	1513.0	99.4
0°-60°	1519.6	99.8
0°-90°	1522.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1522.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10780	
5°	9321	774
15°	1940	614
25°	198	106
35°	26	19
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1299607

CATALOG NUMBER: P3A17R20W2N902765DE010 E3CD1MB_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	10780.0
1°	10728.2
2°	10523.4
3°	10194.5
4°	9809.0
5°	9321.0
6°	8762.0
7°	8111.5
8°	7370.6
9°	6538.1
10°	5693.6
12.5°	3591.3
15°	1939.6
17.5°	1036.1
20°	579.5
22.5°	331.3
25°	197.6
27.5°	120.5
30°	69.9
32.5°	41.0
35°	26.5
37.5°	18.1
40°	13.3
42.5°	8.4
45°	4.8
47.5°	2.4
50°	2.4
52.5°	2.4
55°	2.4
57.5°	2.4
60°	2.4
62.5°	1.2
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)