

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296789

Luminaire Tested: P3A13R35W2N902765DE010 E3CB1MB_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902765DE010 E3CB1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 880.1 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296789

CATALOG NUMBER: P3A13R35W2N902765DE010 E3CB1MB_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1296789

CATALOG NUMBER: P3A13R35W2N902765DE010 E3CB1MB_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98		96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94		93
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94	92	90		89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87		86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84		83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81		80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79		77
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76		75
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79	76	74		73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	71		70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	573814
5°	562138
10°	522947
15°	383407
20°	196320
25°	70770
30°	27549
35°	9637
40°	3979
45°	1085
50°	955
55°	1070
60°	921
65°	726
70°	898
75°	1186
80°	884
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1186 cd/sqm

TEST NUMBER: P1296789

CATALOG NUMBER: P3A13R35W2N902765DE010 E3CB1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	238.1	27.1
10°-20°	446.7	50.8
20°-30°	158.1	18.0
30°-40°	27.7	3.1
40°-50°	4.1	0.5
50°-60°	2.3	0.3
60°-70°	1.6	0.2
70°-80°	1.2	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	842.9	95.8
0°-40°	870.6	98.9
0°-60°	876.9	99.6
0°-90°	880.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2617	
5°	2554	238
15°	1689	447
25°	292	158
35°	36	28
45°	4	4
55°	3	2
65°	1	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1296789

CATALOG NUMBER: P3A13R35W2N902765DE010 E3CB1MB_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2616.8
1°	2616.1
2°	2607.8
3°	2591.9
4°	2577.3
5°	2553.8
6°	2529.5
7°	2502.5
8°	2469.2
9°	2417.2
10°	2348.6
11°	2253.7
12°	2139.3
13°	2003.5
14°	1853.8
15°	1688.9
17.5°	1257.8
20°	841.3
22.5°	507.3
25°	292.5
27.5°	174.6
30°	108.8
32.5°	63.1
35°	36.0
37.5°	22.9
40°	13.9
42.5°	6.9
45°	3.5
47.5°	2.8
50°	2.8
52.5°	2.8
55°	2.8
57.5°	2.1
60°	2.1
62.5°	2.1
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0



TEST NUMBER: P1296789

CATALOG NUMBER: P3A13R35W2N902765DE010 E3CB1MB_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)