

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296853

Luminaire Tested: P3A13R35W2N902765DE010 E3DL1MW\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1296853  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R35W2N902765DE010 E3DL1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 811.0 lumens  
Efficiency: N/A  
Efficacy: 65.9 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296853

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1296853

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 78  |  | 76  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  |  | 81  | 77  | 75  |  | 80  | 77  | 74  |  | 73  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |  | 70  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 66  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 68  | 65  |  | 64  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  |  | 69  | 65  | 62  |  | 69  | 65  | 62  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 409024 |
| 5°  | 393109 |
| 10° | 342523 |
| 15° | 262340 |
| 20° | 175529 |
| 25° | 106192 |
| 30° | 60946  |
| 35° | 34077  |
| 40° | 18120  |
| 45° | 9334   |
| 50° | 4469   |
| 55° | 3555   |
| 60° | 3377   |
| 65° | 2802   |
| 70° | 2949   |
| 75° | 2626   |
| 80° | 2904   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 9334 cd/sqm

TEST NUMBER: P1296853

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 162.5  | 20.0      |
| 10°-20°   | 314.9  | 38.8      |
| 20°-30°   | 206.2  | 25.4      |
| 30°-40°   | 83.6   | 10.3      |
| 40°-50°   | 25.1   | 3.1       |
| 50°-60°   | 8.5    | 1.1       |
| 60°-70°   | 5.7    | 0.7       |
| 70°-80°   | 3.4    | 0.4       |
| 80°-90°   | 1.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 683.5  | 84.3      |
| 0°-40°    | 767.2  | 94.6      |
| 0°-60°    | 800.8  | 98.7      |
| 0°-90°    | 811.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 811.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1865 |      |
| 5°  | 1786 | 162  |
| 15° | 1156 | 315  |
| 25° | 439  | 206  |
| 35° | 127  | 84   |
| 45° | 30   | 25   |
| 55° | 9    | 9    |
| 65° | 5    | 6    |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1296853

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1865.3 |
| 1°    | 1862.3 |
| 2°    | 1853.8 |
| 3°    | 1836.8 |
| 4°    | 1816.7 |
| 5°    | 1785.9 |
| 6°    | 1747.3 |
| 7°    | 1704.1 |
| 8°    | 1655.5 |
| 9°    | 1600.0 |
| 10°   | 1538.3 |
| 11°   | 1469.6 |
| 12°   | 1397.8 |
| 13°   | 1317.6 |
| 14°   | 1241.2 |
| 15°   | 1155.6 |
| 17.5° | 948.1  |
| 20°   | 752.2  |
| 22.5° | 578.6  |
| 25°   | 438.9  |
| 27.5° | 327.1  |
| 30°   | 240.7  |
| 32.5° | 176.7  |
| 35°   | 127.3  |
| 37.5° | 90.3   |
| 40°   | 63.3   |
| 42.5° | 44.0   |
| 45°   | 30.1   |
| 47.5° | 20.1   |
| 50°   | 13.1   |
| 52.5° | 10.0   |
| 55°   | 9.3    |
| 57.5° | 8.5    |
| 60°   | 7.7    |
| 62.5° | 6.9    |
| 65°   | 5.4    |
| 67.5° | 4.6    |
| 70°   | 4.6    |
| 72.5° | 3.9    |
| 75°   | 3.1    |
| 77.5° | 2.3    |
| 80°   | 2.3    |
| 82.5° | 1.5    |
| 85°   | 0.8    |
| 87.5° | 0.8    |



TEST NUMBER: P1296853

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)