

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299696

Luminaire Tested: P3A17R20W2N902765DE010 E3DLD1LI\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1299696  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R20W2N902765DE010 E3DLD1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 948.9 lumens  
Efficiency: N/A  
Efficacy: 48.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299696

CATALOG NUMBER: P3A17R20W2N902765DE010 E3DLD1LI\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1299696

CATALOG NUMBER: P3A17R20W2N902765DE010 E3DLD1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  | 95  | 93  | 91  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 90  | 87  | 85  | 83  |
| 3   | 100 | 93  | 87  | 82  | 98  | 91  | 86  | 82  | 88  | 84  | 80  |  | 86  | 82  | 79  |  | 84  | 81  | 78  | 76  |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 72  |  | 78  | 75  | 72  | 70  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 71  | 67  |  | 75  | 70  | 67  |  | 73  | 69  | 66  | 65  |
| 6   | 84  | 74  | 68  | 63  | 82  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 61  | 60  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  | 60  | 57  | 55  |
| 8   | 75  | 65  | 59  | 54  | 74  | 64  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 53  |  | 61  | 57  | 53  | 52  |
| 9   | 72  | 61  | 55  | 50  | 70  | 61  | 55  | 50  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  | 53  | 50  | 48  |
| 10  | 68  | 58  | 51  | 47  | 67  | 57  | 51  | 47  | 56  | 51  | 47  |  | 56  | 51  | 47  |  | 55  | 50  | 47  | 45  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 234740 |
| 5°  | 228461 |
| 10° | 210172 |
| 15° | 184995 |
| 20° | 158657 |
| 25° | 133290 |
| 30° | 107738 |
| 35° | 81967  |
| 40° | 58309  |
| 45° | 38516  |
| 50° | 23846  |
| 55° | 15674  |
| 60° | 14253  |
| 65° | 13127  |
| 70° | 12374  |
| 75° | 11268  |
| 80° | 10607  |
| 85° | 9057   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38516 cd/sqm

TEST NUMBER: P1299696

CATALOG NUMBER: P3A17R20W2N902765DE010 E3DLD1LI\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 96.0   | 10.1      |
| 10°-20°   | 226.9  | 23.9      |
| 20°-30°   | 251.8  | 26.5      |
| 30°-40°   | 192.1  | 20.2      |
| 40°-50°   | 98.4   | 10.4      |
| 50°-60°   | 40.4   | 4.3       |
| 60°-70°   | 25.2   | 2.7       |
| 70°-80°   | 14.1   | 1.5       |
| 80°-90°   | 4.1    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 574.7  | 60.6      |
| 0°-40°    | 766.8  | 80.8      |
| 0°-60°    | 905.5  | 95.4      |
| 0°-90°    | 948.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 948.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1070 |      |
| 5°  | 1038 | 96   |
| 15° | 815  | 227  |
| 25° | 551  | 252  |
| 35° | 306  | 192  |
| 45° | 124  | 98   |
| 55° | 41   | 40   |
| 65° | 25   | 25   |
| 75° | 13   | 14   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1299696

CATALOG NUMBER: P3A17R20W2N902765DE010 E3DLD1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1070.5 |
| 1°    | 1071.7 |
| 2°    | 1066.9 |
| 3°    | 1060.8 |
| 4°    | 1051.2 |
| 5°    | 1037.9 |
| 6°    | 1022.3 |
| 7°    | 1005.4 |
| 8°    | 987.3  |
| 9°    | 965.6  |
| 10°   | 943.9  |
| 12.5° | 881.2  |
| 15°   | 814.9  |
| 17.5° | 747.4  |
| 20°   | 679.9  |
| 22.5° | 612.4  |
| 25°   | 550.9  |
| 27.5° | 489.4  |
| 30°   | 425.5  |
| 32.5° | 365.3  |
| 35°   | 306.2  |
| 37.5° | 254.4  |
| 40°   | 203.7  |
| 42.5° | 160.3  |
| 45°   | 124.2  |
| 47.5° | 94.0   |
| 50°   | 69.9   |
| 52.5° | 51.8   |
| 55°   | 41.0   |
| 57.5° | 37.4   |
| 60°   | 32.5   |
| 62.5° | 28.9   |
| 65°   | 25.3   |
| 67.5° | 21.7   |
| 70°   | 19.3   |
| 72.5° | 15.7   |
| 75°   | 13.3   |
| 77.5° | 10.8   |
| 80°   | 8.4    |
| 82.5° | 6.0    |
| 85°   | 3.6    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)