

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296908

Luminaire Tested: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 245.0 lumens
Efficiency: N/A
Efficacy: 19.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296908

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296908

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91	89	87	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82	78	76	74
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77	74	71	69
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73	69	66	65
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69	65	62	61
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66	62	59	57
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63	59	56	54
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60	56	53	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	78744
5°	76799
10°	70228
15°	59614
20°	47184
25°	35688
30°	25979
35°	17561
40°	10792
45°	6202
50°	3718
55°	3020
60°	2631
65°	2335
70°	1923
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6202 cd/sqm

TEST NUMBER: P1296908

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.2	13.2
10°-20°	72.4	29.5
20°-30°	67.7	27.6
30°-40°	41.4	16.9
40°-50°	16.3	6.7
50°-60°	7.2	2.9
60°-70°	4.5	1.8
70°-80°	2.4	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.3	70.3
0°-40°	213.8	87.3
0°-60°	237.3	96.9
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	359	
5°	349	32
15°	263	72
25°	148	68
35°	66	41
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1296908

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	359.1
1°	359.5
2°	358.4
3°	356.1
4°	352.7
5°	348.9
6°	344.0
7°	338.4
8°	331.6
9°	324.0
10°	315.4
11°	306.3
12°	296.5
13°	285.9
14°	274.2
15°	262.6
17.5°	232.4
20°	202.2
22.5°	173.2
25°	147.5
27.5°	123.7
30°	102.6
32.5°	83.0
35°	65.6
37.5°	50.2
40°	37.7
42.5°	27.2
45°	20.0
47.5°	14.3
50°	10.9
52.5°	9.1
55°	7.9
57.5°	6.8
60°	6.0
62.5°	5.3
65°	4.5
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4



TEST NUMBER: P1296908

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)