

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297061

Luminaire Tested: P3A13R40W2N902750DE010 E3DLD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R40W2N902750DE010 E3DLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297061

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297061

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96	94	93		91			
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89	87	85		83			
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	78		76			
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71		69			
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73	69	66		64			
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68	64	61		59			
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64	60	56		55			
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61	56	52		51			
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57	52	49		48			
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54	49	46		45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	154659
5°	151860
10°	143150
15°	130012
20°	114227
25°	97554
30°	80797
35°	62319
40°	44340
45°	29895
50°	16307
55°	11507
60°	10832
65°	10014
70°	8912
75°	8472
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29895 cd/sqm

TEST NUMBER: P1297061

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	9.3
10°-20°	159.5	23.2
20°-30°	184.5	26.8
30°-40°	145.3	21.1
40°-50°	74.6	10.8
50°-60°	28.5	4.1
60°-70°	18.9	2.7
70°-80°	10.3	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.3	59.3
0°-40°	553.7	80.4
0°-60°	656.8	95.3
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	690	64
15°	573	160
25°	403	184
35°	233	145
45°	96	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1297061

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	705.3
2.5°	701.5
5°	689.9
7.5°	669.9
10°	642.9
12.5°	611.3
15°	572.7
17.5°	532.7
20°	489.5
22.5°	445.6
25°	403.2
27.5°	360.8
30°	319.1
32.5°	276.7
35°	232.8
37.5°	191.9
40°	154.9
42.5°	123.3
45°	96.4
47.5°	70.1
50°	47.8
52.5°	34.7
55°	30.1
57.5°	27.0
60°	24.7
62.5°	21.6
65°	19.3
67.5°	16.2
70°	13.9
72.5°	11.6
75°	10.0
77.5°	7.7
80°	5.4
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)