

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300087

Luminaire Tested: P3A17R25W2N902765DE010 E3PHLP1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R25W2N902765DE010 E3PHLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 35.5 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300087

CATALOG NUMBER: P3A17R25W2N902765DE010 E3PHLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1300087

CATALOG NUMBER: P3A17R25W2N902765DE010 E3PHLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	73	81	76	72		79	74	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	66		72
6	84	74	67	62	82	73	66	62	71	66	61		70	65	61		68
7	79	69	63	58	78	68	62	58	67	61	57		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231495
5°	218710
10°	185902
15°	147243
20°	111916
25°	83473
30°	60718
35°	42938
40°	29140
45°	20343
50°	17057
55°	16477
60°	17411
65°	17901
70°	17695
75°	18978
80°	21846
85°	21637

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 23184 cd/sqm

TEST NUMBER: P1300087

CATALOG NUMBER: P3A17R25W2N902765DE010 E3PHLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	13.0
10°-20°	179.5	26.1
20°-30°	159.0	23.1
30°-40°	101.3	14.7
40°-50°	53.6	7.8
50°-60°	39.4	5.7
60°-70°	33.5	4.9
70°-80°	23.7	3.4
80°-90°	9.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.2	62.1
0°-40°	529.5	76.8
0°-60°	622.4	90.3
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	994	90
15°	649	180
25°	345	159
35°	160	101
45°	66	54
55°	43	39
65°	34	34
75°	22	24
85°	9	9
90°	0	

TEST NUMBER: P1300087

CATALOG NUMBER: P3A17R25W2N902765DE010 E3PHLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1055.7
2.5°	1040.2
5°	993.6
7.5°	921.2
10°	834.9
12.5°	741.8
15°	648.6
17.5°	558.9
20°	479.6
22.5°	407.1
25°	345.0
27.5°	289.8
30°	239.8
32.5°	196.7
35°	160.4
37.5°	127.7
40°	101.8
42.5°	81.1
45°	65.6
47.5°	56.9
50°	50.0
52.5°	46.6
55°	43.1
57.5°	41.4
60°	39.7
62.5°	36.2
65°	34.5
67.5°	31.1
70°	27.6
72.5°	25.9
75°	22.4
77.5°	19.0
80°	17.3
82.5°	13.8
85°	8.6
87.5°	3.5
90°	0.0

(END OF REPORT)