

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300326

Luminaire Tested: P3A17R30W2N902765DE010 E3DL1H\_3500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1300326  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R30W2N902765DE010 E3DL1H\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1283.0 lumens  
Efficiency: N/A  
Efficacy: 66.1 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1300326

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DL1H\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1300326

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DL1H\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  | 95  |
| 2   | 110 | 105 | 102 | 99  | 107 | 104 | 101 | 98  | 101 | 98  | 96  |  | 98  | 96  | 94  |  | 95  | 93  | 92  | 90  |
| 3   | 105 | 100 | 96  | 92  | 103 | 98  | 95  | 91  | 96  | 93  | 90  |  | 94  | 91  | 89  |  | 91  | 89  | 87  | 86  |
| 4   | 101 | 95  | 90  | 87  | 99  | 94  | 89  | 86  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  | 82  |
| 5   | 97  | 90  | 85  | 82  | 96  | 89  | 85  | 81  | 88  | 84  | 81  |  | 86  | 83  | 80  |  | 85  | 82  | 79  | 78  |
| 6   | 94  | 86  | 81  | 78  | 92  | 85  | 81  | 77  | 84  | 80  | 77  |  | 83  | 79  | 76  |  | 81  | 78  | 76  | 75  |
| 7   | 90  | 82  | 77  | 74  | 89  | 82  | 77  | 74  | 81  | 76  | 73  |  | 80  | 76  | 73  |  | 79  | 75  | 73  | 71  |
| 8   | 87  | 79  | 74  | 71  | 86  | 79  | 74  | 71  | 78  | 73  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 70  | 69  |
| 9   | 84  | 76  | 71  | 68  | 83  | 75  | 71  | 68  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 70  | 67  | 66  |
| 10  | 81  | 73  | 68  | 65  | 80  | 73  | 68  | 65  | 72  | 68  | 65  |  | 71  | 67  | 65  |  | 71  | 67  | 65  | 63  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 748668 |
| 5°  | 712589 |
| 10° | 599388 |
| 15° | 432261 |
| 20° | 268123 |
| 25° | 152477 |
| 30° | 84697  |
| 35° | 46070  |
| 40° | 24274  |
| 45° | 13149  |
| 50° | 7027   |
| 55° | 4626   |
| 60° | 4254   |
| 65° | 4410   |
| 70° | 3911   |
| 75° | 3050   |
| 80° | 3031   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13149 cd/sqm

TEST NUMBER: P1300326

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DL1H\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 291.5  | 22.7      |
| 10°-20°   | 518.2  | 40.4      |
| 20°-30°   | 299.5  | 23.3      |
| 30°-40°   | 113.7  | 8.9       |
| 40°-50°   | 34.9   | 2.7       |
| 50°-60°   | 11.7   | 0.9       |
| 60°-70°   | 8.0    | 0.6       |
| 70°-80°   | 4.3    | 0.3       |
| 80°-90°   | 1.3    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1109.1 | 86.5      |
| 0°-40°    | 1222.8 | 95.3      |
| 0°-60°    | 1269.4 | 98.9      |
| 0°-90°    | 1283.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1283.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3414 |      |
| 5°  | 3237 | 291  |
| 15° | 1904 | 518  |
| 25° | 630  | 299  |
| 35° | 172  | 114  |
| 45° | 42   | 35   |
| 55° | 12   | 12   |
| 65° | 8    | 8    |
| 75° | 4    | 4    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1300326

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DL1H\_3500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3414.2 |
| 1°    | 3411.8 |
| 2°    | 3391.2 |
| 3°    | 3352.4 |
| 4°    | 3303.9 |
| 5°    | 3237.3 |
| 6°    | 3152.4 |
| 7°    | 3057.9 |
| 8°    | 2952.4 |
| 9°    | 2826.4 |
| 10°   | 2691.9 |
| 11°   | 2546.4 |
| 12°   | 2392.5 |
| 13°   | 2231.3 |
| 14°   | 2067.7 |
| 15°   | 1904.1 |
| 17.5° | 1501.7 |
| 20°   | 1149.0 |
| 22.5° | 852.0  |
| 25°   | 630.2  |
| 27.5° | 458.1  |
| 30°   | 334.5  |
| 32.5° | 241.2  |
| 35°   | 172.1  |
| 37.5° | 120.0  |
| 40°   | 84.8   |
| 42.5° | 59.4   |
| 45°   | 42.4   |
| 47.5° | 29.1   |
| 50°   | 20.6   |
| 52.5° | 14.5   |
| 55°   | 12.1   |
| 57.5° | 10.9   |
| 60°   | 9.7    |
| 62.5° | 8.5    |
| 65°   | 8.5    |
| 67.5° | 7.3    |
| 70°   | 6.1    |
| 72.5° | 4.8    |
| 75°   | 3.6    |
| 77.5° | 3.6    |
| 80°   | 2.4    |
| 82.5° | 2.4    |
| 85°   | 1.2    |
| 87.5° | 0.0    |



TEST NUMBER: P1300326

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DL1H\_3500K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)