

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300392

Luminaire Tested: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R30W2N902765DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 383.1 lumens
Efficiency: N/A
Efficacy: 19.7 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300392

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1300392

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74		
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61		
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58		
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55		
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130889
5°	126810
10°	114249
15°	94507
20°	73180
25°	54898
30°	39854
35°	26555
40°	16316
45°	9582
50°	5868
55°	4779
60°	4166
65°	3373
70°	3077
75°	3050
80°	2273
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9582 cd/sqm

TEST NUMBER: P1300392

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.0	13.8
10°-20°	114.7	29.9
20°-30°	104.3	27.2
30°-40°	63.1	16.5
40°-50°	25.3	6.6
50°-60°	11.2	2.9
60°-70°	6.7	1.8
70°-80°	3.7	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.0	71.0
0°-40°	335.0	87.5
0°-60°	371.5	97.0
0°-90°	383.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	383.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	597	
5°	576	53
15°	416	115
25°	227	104
35°	99	63
45°	31	25
55°	12	11
65°	6	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1300392

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	596.9
1°	596.3
2°	593.9
3°	589.7
4°	583.8
5°	576.1
6°	566.6
7°	556.5
8°	543.4
9°	528.6
10°	513.1
11°	495.3
12°	476.3
13°	457.3
14°	436.5
15°	416.3
17.5°	363.5
20°	313.6
22.5°	267.2
25°	226.9
27.5°	190.0
30°	157.4
32.5°	127.1
35°	99.2
37.5°	76.0
40°	57.0
42.5°	41.6
45°	30.9
47.5°	23.2
50°	17.2
52.5°	13.7
55°	12.5
57.5°	10.7
60°	9.5
62.5°	7.7
65°	6.5
67.5°	5.9
70°	4.8
72.5°	4.2
75°	3.6
77.5°	3.0
80°	1.8
82.5°	1.2
85°	1.2
87.5°	0.6



TEST NUMBER: P1300392

CATALOG NUMBER: P3A17R30W2N902765DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)