

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1300449

Luminaire Tested: P3A17R35W2N902750DE010 E3CB1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1300449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R35W2N902750DE010 E3CB1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1375.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1300449

CATALOG NUMBER: P3A17R35W2N902750DE010 E3CB1MMS_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1300449

CATALOG NUMBER: P3A17R35W2N902750DE010 E3CB1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99	99	98		96
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97	95	94		93
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94	92	90		89
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91	89	87		86
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89	86	84		83
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86	83	81		80
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84	81	79		78
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81	78	76		75
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79	76	74		73
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77	74	71		70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	896595
5°	878316
10°	817108
15°	599073
20°	306767
25°	110571
30°	43045
35°	15071
40°	6212
45°	1675
50°	1467
55°	1644
60°	1403
65°	1141
70°	1410
75°	1864
80°	1389
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1864 cd/sqm

TEST NUMBER: P1300449

CATALOG NUMBER: P3A17R35W2N902750DE010 E3CB1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	372.0	27.1
10°-20°	698.0	50.8
20°-30°	247.1	18.0
30°-40°	43.3	3.1
40°-50°	6.3	0.5
50°-60°	3.5	0.3
60°-70°	2.5	0.2
70°-80°	1.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1317.1	95.8
0°-40°	1360.3	98.9
0°-60°	1370.1	99.6
0°-90°	1375.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4089	
5°	3990	372
15°	2639	698
25°	457	247
35°	56	43
45°	5	6
55°	4	3
65°	2	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1300449

CATALOG NUMBER: P3A17R35W2N902750DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4088.8
1°	4087.7
2°	4074.7
3°	4049.8
4°	4027.1
5°	3990.2
6°	3952.3
7°	3910.1
8°	3858.1
9°	3776.9
10°	3669.7
11°	3521.4
12°	3342.7
13°	3130.5
14°	2896.6
15°	2638.9
17.5°	1965.3
20°	1314.6
22.5°	792.6
25°	457.0
27.5°	272.9
30°	170.0
32.5°	98.5
35°	56.3
37.5°	35.7
40°	21.7
42.5°	10.8
45°	5.4
47.5°	4.3
50°	4.3
52.5°	4.3
55°	4.3
57.5°	3.2
60°	3.2
62.5°	3.2
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0



TEST NUMBER: P1300449

CATALOG NUMBER: P3A17R35W2N902750DE010 E3CB1MMS_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)