

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297682

Luminaire Tested: P3A13R50W2N902750DE010 E3DLP1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297682  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R50W2N902750DE010 E3DLP1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 564.0 lumens  
Efficiency: N/A  
Efficacy: 45.9 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297682  
CATALOG NUMBER: P3A13R50W2N902750DE010 E3DLP1MW\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1297682  
 CATALOG NUMBER: P3A13R50W2N902750DE010 E3DLP1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																	
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100																
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93																
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85																
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79																
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73																
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68																
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64																
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60																
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56																
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53																
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50																

**AVERAGE LUMINANCE (cd/sqm):**

0°	
0°	164044
5°	159630
10°	147203
15°	129445
20°	108299
25°	85892
30°	62997
35°	43313
40°	27537
45°	15381
50°	8324
55°	6996
60°	6008
65°	5552
70°	4873
75°	4490
80°	3915
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15381 cd/sqm



TEST NUMBER: P1297682

CATALOG NUMBER: P3A13R50W2N902750DE010 E3DLP1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.2	11.9
10°-20°	157.9	28.0
20°-30°	161.5	28.6
30°-40°	102.4	18.2
40°-50°	40.8	7.2
50°-60°	16.5	2.9
60°-70°	10.6	1.9
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.6	68.6
0°-40°	489.0	86.7
0°-60°	546.3	96.9
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	748	
5°	725	67
15°	570	158
25°	355	162
35°	162	102
45°	50	41
55°	18	16
65°	11	11
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1297682  
CATALOG NUMBER: P3A13R50W2N902750DE010 E3DLP1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	748.1
2.5°	742.7
5°	725.2
7.5°	697.7
10°	661.1
12.5°	617.5
15°	570.2
17.5°	518.3
20°	464.1
22.5°	409.9
25°	355.0
27.5°	300.0
30°	248.8
32.5°	203.0
35°	161.8
37.5°	126.7
40°	96.2
42.5°	71.0
45°	49.6
47.5°	33.6
50°	24.4
52.5°	20.6
55°	18.3
57.5°	16.0
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)