

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301107

Luminaire Tested: P3A17R45W2N902750DE010 E3DL1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301107  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R45W2N902750DE010 E3DL1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 654.0 lumens  
Efficiency: N/A  
Efficacy: 33.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301107  
CATALOG NUMBER: P3A17R45W2N902750DE010 E3DL1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301107

CATALOG NUMBER: P3A17R45W2N902750DE010 E3DL1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	245594
5°	239841
10°	220481
15°	186812
20°	144936
25°	101328
30°	63833
35°	37584
40°	21268
45°	10327
50°	3582
55°	2906
60°	2807
65°	2750
70°	2629
75°	2457
80°	2273
85°	1510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10327 cd/sqm



TEST NUMBER: P1301107

CATALOG NUMBER: P3A17R45W2N902750DE010 E3DL1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	100.9	15.4
10°-20°	226.0	34.6
20°-30°	191.9	29.3
30°-40°	91.5	14.0
40°-50°	27.6	4.2
50°-60°	7.0	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.7	79.3
0°-40°	610.3	93.3
0°-60°	644.8	98.6
0°-90°	654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	654.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1120	
5°	1090	101
15°	823	226
25°	419	192
35°	140	92
45°	33	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1301107

CATALOG NUMBER: P3A17R45W2N902750DE010 E3DL1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1120.0
2.5°	1113.0
5°	1089.6
7.5°	1049.3
10°	990.2
12.5°	911.8
15°	822.9
17.5°	724.1
20°	621.1
22.5°	516.4
25°	418.8
27.5°	329.9
30°	252.1
32.5°	189.5
35°	140.4
37.5°	103.5
40°	74.3
42.5°	51.5
45°	33.3
47.5°	18.7
50°	10.5
52.5°	8.2
55°	7.6
57.5°	7.0
60°	6.4
62.5°	5.8
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	2.9
77.5°	2.3
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)