

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297919

Luminaire Tested: P3A13R55W2N902750DE010 E3D1WH\_5000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1297919  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R55W2N902750DE010 E3D1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 995.0 lumens  
Efficiency: N/A  
Efficacy: 80.9 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297919

CATALOG NUMBER: P3A13R55W2N902750DE010 E3D1WH\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1297919

CATALOG NUMBER: P3A13R55W2N902750DE010 E3D1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 95  |    |    |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 92  | 91  | 89  |    |    |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 84  |    |    |
| 4   | 100 | 93  | 88  | 84  | 98  | 92  | 87  | 84  | 90  | 86  | 83  | 88  | 84  | 82  | 86  | 83  | 81  | 79  |    |    |
| 5   | 95  | 88  | 82  | 79  | 94  | 87  | 82  | 78  | 85  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 75  |    |    |
| 6   | 91  | 83  | 78  | 74  | 90  | 82  | 77  | 74  | 81  | 76  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 71  |    |    |
| 7   | 87  | 79  | 73  | 70  | 86  | 78  | 73  | 69  | 77  | 72  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |
| 8   | 83  | 75  | 69  | 66  | 82  | 74  | 69  | 65  | 73  | 69  | 65  | 72  | 68  | 65  | 71  | 68  | 65  | 63  |    |    |
| 9   | 80  | 71  | 66  | 62  | 79  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 62  | 68  | 64  | 61  | 60  |    |    |
| 10  | 77  | 68  | 62  | 59  | 76  | 67  | 62  | 59  | 67  | 62  | 59  | 66  | 62  | 59  | 65  | 61  | 58  | 57  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 288530 |
| 5°  | 278318 |
| 10° | 288282 |
| 15° | 284224 |
| 20° | 263036 |
| 25° | 212722 |
| 30° | 127488 |
| 35° | 43206  |
| 40° | 11908  |
| 45° | 5272   |
| 50° | 1535   |
| 55° | 306    |
| 60° | 175    |
| 65° | 208    |
| 70° | 256    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5272 cd/sqm

TEST NUMBER: P1297919

CATALOG NUMBER: P3A13R55W2N902750DE010 E3D1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 122.3  | 12.3      |
| 10°-20°   | 348.6  | 35.0      |
| 20°-30°   | 387.5  | 38.9      |
| 30°-40°   | 120.6  | 12.1      |
| 40°-50°   | 14.5   | 1.5       |
| 50°-60°   | 1.1    | 0.1       |
| 60°-70°   | 0.4    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 858.4  | 86.3      |
| 0°-40°    | 979.0  | 98.4      |
| 0°-60°    | 994.6  | 100.0     |
| 0°-90°    | 995.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 995.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1316 |      |
| 5°  | 1264 | 122  |
| 15° | 1252 | 349  |
| 25° | 879  | 387  |
| 35° | 161  | 121  |
| 45° | 17   | 14   |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1297919

CATALOG NUMBER: P3A13R55W2N902750DE010 E3D1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1315.8 |
| 1°    | 1310.9 |
| 2°    | 1298.1 |
| 3°    | 1282.2 |
| 4°    | 1267.8 |
| 5°    | 1264.4 |
| 6°    | 1268.2 |
| 7°    | 1276.2 |
| 8°    | 1285.2 |
| 9°    | 1292.4 |
| 10°   | 1294.7 |
| 11°   | 1293.2 |
| 12°   | 1287.1 |
| 13°   | 1277.7 |
| 14°   | 1266.7 |
| 15°   | 1252.0 |
| 16°   | 1234.9 |
| 17°   | 1213.4 |
| 18°   | 1189.2 |
| 19°   | 1160.1 |
| 20°   | 1127.2 |
| 21°   | 1089.8 |
| 22°   | 1045.6 |
| 23°   | 996.8  |
| 24°   | 940.9  |
| 25°   | 879.2  |
| 26°   | 811.6  |
| 27°   | 739.8  |
| 28°   | 663.0  |
| 29°   | 584.0  |
| 30°   | 503.5  |
| 31°   | 422.6  |
| 32°   | 343.6  |
| 32.5° | 308.5  |
| 33°   | 272.2  |
| 34°   | 210.5  |
| 35°   | 161.4  |
| 36°   | 122.9  |
| 37°   | 91.1   |
| 37.5° | 77.9   |
| 38°   | 67.7   |
| 39°   | 51.4   |
| 40°   | 41.6   |
| 42.5° | 26.5   |
| 45°   | 17.0   |



TEST NUMBER: P1297919

CATALOG NUMBER: P3A13R55W2N902750DE010 E3D1WH\_5000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 10.2 |
| 50°   | 4.5  |
| 52.5° | 1.5  |
| 55°   | 0.8  |
| 57.5° | 0.4  |
| 60°   | 0.4  |
| 62.5° | 0.4  |
| 65°   | 0.4  |
| 67.5° | 0.4  |
| 70°   | 0.4  |
| 72.5° | 0.0  |
| 75°   | 0.0  |
| 77.5° | 0.0  |
| 80°   | 0.0  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)