

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301255

Luminaire Tested: P3A17R45W2N902765DE010 E3DL1LI\_6500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1301255  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R45W2N902765DE010 E3DL1LI\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 6500K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1347.0 lumens  
Efficiency: N/A  
Efficacy: 69.4 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301255

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1LI\_6500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1301255

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1LI\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  | 97  | 96  |  | 94  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  |  | 96  | 94  | 92  |  | 93  | 91  | 90  |  | 88  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  |  | 91  | 88  | 86  |  | 89  | 87  | 84  |  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  |  | 82  | 79  | 76  |  | 81  | 78  | 75  |  | 74  |
| 6   | 90  | 82  | 77  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  |  | 78  | 74  | 71  |  | 77  | 74  | 71  |  | 70  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  | 70  | 67  |  | 66  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 65  | 72  | 68  | 64  |  | 71  | 67  | 64  |  | 70  | 67  | 64  |  | 62  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  | 63  | 61  |  | 59  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  | 61  | 58  |  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 505837 |
| 5°  | 493989 |
| 10° | 454100 |
| 15° | 384770 |
| 20° | 298529 |
| 25° | 208681 |
| 30° | 131463 |
| 35° | 77390  |
| 40° | 43796  |
| 45° | 21305  |
| 50° | 7403   |
| 55° | 6002   |
| 60° | 5833   |
| 65° | 5604   |
| 70° | 5386   |
| 75° | 5083   |
| 80° | 4546   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21305 cd/sqm

TEST NUMBER: P1301255

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1LI\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 207.7  | 15.4      |
| 10°-20°   | 465.4  | 34.6      |
| 20°-30°   | 395.2  | 29.3      |
| 30°-40°   | 188.5  | 14.0      |
| 40°-50°   | 56.8   | 4.2       |
| 50°-60°   | 14.4   | 1.1       |
| 60°-70°   | 10.7   | 0.8       |
| 70°-80°   | 6.3    | 0.5       |
| 80°-90°   | 1.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1068.4 | 79.3      |
| 0°-40°    | 1256.9 | 93.3      |
| 0°-60°    | 1328.1 | 98.6      |
| 0°-90°    | 1347.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1347.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2307 |      |
| 5°  | 2244 | 208  |
| 15° | 1695 | 465  |
| 25° | 862  | 395  |
| 35° | 289  | 189  |
| 45° | 69   | 57   |
| 55° | 16   | 14   |
| 65° | 11   | 11   |
| 75° | 6    | 6    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1301255

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DL1LI\_6500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2306.8 |
| 2.5°  | 2292.4 |
| 5°    | 2244.2 |
| 7.5°  | 2161.1 |
| 10°   | 2039.4 |
| 12.5° | 1878.0 |
| 15°   | 1694.9 |
| 17.5° | 1491.3 |
| 20°   | 1279.3 |
| 22.5° | 1063.7 |
| 25°   | 862.5  |
| 27.5° | 679.4  |
| 30°   | 519.2  |
| 32.5° | 390.3  |
| 35°   | 289.1  |
| 37.5° | 213.2  |
| 40°   | 153.0  |
| 42.5° | 106.0  |
| 45°   | 68.7   |
| 47.5° | 38.5   |
| 50°   | 21.7   |
| 52.5° | 16.9   |
| 55°   | 15.7   |
| 57.5° | 14.5   |
| 60°   | 13.3   |
| 62.5° | 12.0   |
| 65°   | 10.8   |
| 67.5° | 9.6    |
| 70°   | 8.4    |
| 72.5° | 7.2    |
| 75°   | 6.0    |
| 77.5° | 4.8    |
| 80°   | 3.6    |
| 82.5° | 2.4    |
| 85°   | 1.2    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)