

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298005

Luminaire Tested: P3A13R55W2N902750DE010 E3DLP1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298005  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R55W2N902750DE010 E3DLP1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 755.0 lumens  
Efficiency: N/A  
Efficacy: 61.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298005  
CATALOG NUMBER: P3A13R55W2N902750DE010 E3DLP1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298005

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DLP1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93	93	93	93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87	87	87	87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81	81	81	81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55	55	55	55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	207308
5°	205216
10°	198170
15°	183179
20°	158074
25°	124846
30°	88571
35°	57099
40°	34293
45°	19320
50°	10405
55°	3708
60°	3333
65°	3217
70°	3077
75°	2965
80°	2652
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19320 cd/sqm



TEST NUMBER: P1298005

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DLP1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.7	11.6
10°-20°	223.1	29.6
20°-30°	233.8	31.0
30°-40°	136.4	18.1
40°-50°	51.0	6.8
50°-60°	12.0	1.6
60°-70°	6.1	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.6	72.1
0°-40°	681.1	90.2
0°-60°	744.1	98.6
0°-90°	755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	945	
5°	932	88
15°	807	223
25°	516	234
35°	213	136
45°	62	51
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1298005  
CATALOG NUMBER: P3A13R55W2N902750DE010 E3DLP1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	945.4
2.5°	942.7
5°	932.3
7.5°	915.7
10°	890.0
12.5°	854.0
15°	806.9
17.5°	747.4
20°	677.4
22.5°	599.1
25°	516.0
27.5°	430.8
30°	349.8
32.5°	276.4
35°	213.3
37.5°	162.1
40°	119.8
42.5°	85.9
45°	62.3
47.5°	45.0
50°	30.5
52.5°	17.3
55°	9.7
57.5°	8.3
60°	7.6
62.5°	6.9
65°	6.2
67.5°	5.5
70°	4.8
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)