

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301332

Luminaire Tested: P3A17R45W2N902765DE010 E3DLP1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1301332  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R45W2N902765DE010 E3DLP1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 5000K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 868.9 lumens  
Efficiency: N/A  
Efficacy: 44.8 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1301332  
CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1301332

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	94	94	94	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	87	87	87	86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	81	81	81	79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	75	75	75	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	70	70	70	69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	66	66	66	64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	61	61	61	60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	58	58	58	56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	55	55	55	53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	52	52	52	50

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	258839
5°	252938
10°	233329
15°	202884
20°	166684
25°	129685
30°	95762
35°	67378
40°	42050
45°	22793
50°	12315
55°	10590
60°	9517
65°	8146
70°	6924
75°	7117
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22793 cd/sqm



TEST NUMBER: P1301332

CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	106.4	12.2
10°-20°	247.1	28.4
20°-30°	245.3	28.2
30°-40°	158.0	18.2
40°-50°	60.8	7.0
50°-60°	24.7	2.8
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.8	68.9
0°-40°	756.7	87.1
0°-60°	842.3	96.9
0°-90°	868.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	868.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1180	
5°	1149	106
15°	894	247
25°	536	245
35°	252	158
45°	74	61
55°	28	25
65°	16	16
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1301332  
CATALOG NUMBER: P3A17R45W2N902765DE010 E3DLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1180.4
2.5°	1174.4
5°	1149.1
7.5°	1105.7
10°	1047.9
12.5°	975.6
15°	893.7
17.5°	804.6
20°	714.3
22.5°	622.7
25°	536.0
27.5°	454.1
30°	378.2
32.5°	312.0
35°	251.7
37.5°	197.5
40°	146.9
42.5°	106.0
45°	73.5
47.5°	49.4
50°	36.1
52.5°	30.1
55°	27.7
57.5°	24.1
60°	21.7
62.5°	18.1
65°	15.7
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)