

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298177

Luminaire Tested: P3A13R55W2N902765DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R55W2N902765DE010 E3DLP1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 755.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298177

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1298177

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLP1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207308
5°	205216
10°	198170
15°	183179
20°	158074
25°	124846
30°	88571
35°	57099
40°	34293
45°	19320
50°	10405
55°	3708
60°	3333
65°	3217
70°	3077
75°	2965
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19320 cd/sqm

TEST NUMBER: P1298177

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	11.6
10°-20°	223.1	29.6
20°-30°	233.8	31.0
30°-40°	136.4	18.1
40°-50°	51.0	6.8
50°-60°	12.0	1.6
60°-70°	6.1	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	544.6	72.1
0°-40°	681.1	90.2
0°-60°	744.1	98.6
0°-90°	755.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	945	
5°	932	88
15°	807	223
25°	516	234
35°	213	136
45°	62	51
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1298177

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	945.4
2.5°	942.7
5°	932.3
7.5°	915.7
10°	890.0
12.5°	854.0
15°	806.9
17.5°	747.4
20°	677.4
22.5°	599.1
25°	516.0
27.5°	430.8
30°	349.8
32.5°	276.4
35°	213.3
37.5°	162.1
40°	119.8
42.5°	85.9
45°	62.3
47.5°	45.0
50°	30.5
52.5°	17.3
55°	9.7
57.5°	8.3
60°	7.6
62.5°	6.9
65°	6.2
67.5°	5.5
70°	4.8
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)