

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1301463

Luminaire Tested: P3A17R50W2N902750DE010 E3DLP1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1301463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R50W2N902750DE010 E3DLP1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 439.0 lumens
Efficiency: N/A
Efficacy: 22.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1301463
CATALOG NUMBER: P3A17R50W2N902750DE010 E3DLP1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1301463

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DLP1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73				73
5	91	83	76	72	90	82	76	72	80	75	71	78	74	70	77	73	70	68				68
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64				64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	61	68	64	61	60				60
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56				56
9	75	65	59	55	74	64	59	55	63	58	55	63	58	54	62	57	54	53				53
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127687
5°	124257
10°	114560
15°	100750
20°	84287
25°	66851
30°	49046
35°	33729
40°	21440
45°	11970
50°	6482
55°	5467
60°	4693
65°	4307
70°	3783
75°	3558
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11970 cd/sqm



TEST NUMBER: P1301463

CATALOG NUMBER: P3A17R50W2N902750DE010 E3DLP1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	11.9
10°-20°	122.9	28.0
20°-30°	125.7	28.6
30°-40°	79.7	18.2
40°-50°	31.7	7.2
50°-60°	12.9	2.9
60°-70°	8.2	1.9
70°-80°	4.3	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.9	68.5
0°-40°	380.7	86.7
0°-60°	425.2	96.9
0°-90°	439.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	439.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	582	
5°	564	52
15°	444	123
25°	276	126
35°	126	80
45°	39	32
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1301463
CATALOG NUMBER: P3A17R50W2N902750DE010 E3DLP1GPH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	582.3
2.5°	578.1
5°	564.5
7.5°	543.1
10°	514.5
12.5°	480.7
15°	443.8
17.5°	403.4
20°	361.2
22.5°	319.1
25°	276.3
27.5°	233.5
30°	193.7
32.5°	158.0
35°	126.0
37.5°	98.6
40°	74.9
42.5°	55.3
45°	38.6
47.5°	26.1
50°	19.0
52.5°	16.0
55°	14.3
57.5°	12.5
60°	10.7
62.5°	9.5
65°	8.3
67.5°	7.1
70°	5.9
72.5°	4.8
75°	4.2
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)