

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298344

Luminaire Tested: P3A13R60W2N902765DE010 E3CB1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902765DE010 E3CB1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 997.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298344

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298344

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		78	70	64	60		69	64	60		68	63	60		67	62	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	238073
5°	228637
10°	235400
15°	238435
20°	210532
25°	177422
30°	143896
35°	93719
40°	43052
45°	16498
50°	5526
55°	1491
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16498 cd/sqm

TEST NUMBER: P1298344

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.0	10.0
10°-20°	287.6	28.8
20°-30°	335.5	33.6
30°-40°	216.5	21.7
40°-50°	48.5	4.9
50°-60°	4.9	0.5
60°-70°	2.3	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.0	72.5
0°-40°	939.5	94.2
0°-60°	992.9	99.6
0°-90°	997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1086	
5°	1039	100
15°	1050	288
25°	733	335
35°	350	216
45°	53	48
55°	4	5
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1298344

CATALOG NUMBER: P3A13R60W2N902765DE010 E3CB1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1085.7
2.5°	1068.0
5°	1038.7
7.5°	1037.1
10°	1057.2
12.5°	1070.3
15°	1050.3
17.5°	990.1
20°	902.2
22.5°	810.4
25°	733.3
27.5°	657.8
30°	568.3
32.5°	463.4
35°	350.1
37.5°	239.0
40°	150.4
42.5°	90.2
45°	53.2
47.5°	30.8
50°	16.2
52.5°	5.4
55°	3.9
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	2.3
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)