

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298648

Luminaire Tested: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298648  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 480.0 lumens  
Efficiency: N/A  
Efficacy: 39.0 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298648  
CATALOG NUMBER: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298648

CATALOG NUMBER: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	122008
5°	118974
10°	110797
15°	99297
20°	85757
25°	71327
30°	56237
35°	41680
40°	28711
45°	17800
50°	9688
55°	6079
60°	5175
65°	4670
70°	3975
75°	3558
80°	3536
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17800 cd/sqm



TEST NUMBER: P1298648

CATALOG NUMBER: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	10.5
10°-20°	121.6	25.3
20°-30°	134.4	28.0
30°-40°	97.6	20.3
40°-50°	45.7	9.5
50°-60°	15.4	3.2
60°-70°	8.9	1.9
70°-80°	4.7	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.2	63.8
0°-40°	403.8	84.1
0°-60°	464.9	96.9
0°-90°	480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	480.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	556	
5°	540	50
15°	437	122
25°	295	134
35°	156	98
45°	57	46
55°	16	15
65°	9	9
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1298648  
CATALOG NUMBER: P3A13R65W2N902750DE010 E3DLP1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	556.4
2.5°	552.9
5°	540.5
7.5°	521.8
10°	497.6
12.5°	469.2
15°	437.4
17.5°	402.8
20°	367.5
22.5°	330.8
25°	294.8
27.5°	258.1
30°	222.1
32.5°	187.5
35°	155.7
37.5°	126.6
40°	100.3
42.5°	76.8
45°	57.4
47.5°	41.5
50°	28.4
52.5°	19.4
55°	15.9
57.5°	13.8
60°	11.8
62.5°	10.4
65°	9.0
67.5°	7.6
70°	6.2
72.5°	5.5
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)