

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1287932

Luminaire Tested: P3A05R15W2N902765DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1287932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRIS
Catalog Number: P3A05R15W2N902765DE010 E3D1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 511.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1287932
CATALOG NUMBER: P3A05R15W2N902765DE010 E3D1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1287932

CATALOG NUMBER: P3A05R15W2N902765DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | | |
| 2 | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99 | 99 | 98 | 97 | 96 | | |
| 3 | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99 | 102 | 100 | 98 | 100 | 98 | 96 | 98 | 96 | 95 | 94 | | |
| 4 | 107 | 102 | 99 | 96 | 105 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 96 | 94 | 96 | 94 | 93 | 92 | | |
| 5 | 105 | 100 | 96 | 94 | 103 | 99 | 96 | 93 | 97 | 94 | 92 | 96 | 93 | 92 | 94 | 93 | 91 | 90 | | |
| 6 | 102 | 97 | 94 | 91 | 101 | 96 | 93 | 91 | 95 | 92 | 90 | 94 | 92 | 90 | 93 | 91 | 89 | 88 | | |
| 7 | 100 | 95 | 91 | 89 | 99 | 94 | 91 | 89 | 93 | 90 | 88 | 92 | 90 | 88 | 91 | 89 | 88 | 87 | | |
| 8 | 98 | 93 | 89 | 87 | 97 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 85 | | |
| 9 | 96 | 91 | 88 | 85 | 96 | 91 | 87 | 85 | 90 | 87 | 85 | 89 | 87 | 85 | 88 | 86 | 85 | 84 | | |
| 10 | 95 | 89 | 86 | 84 | 94 | 89 | 86 | 84 | 88 | 85 | 83 | 88 | 85 | 83 | 87 | 85 | 83 | 82 | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 973080 |
| 5° | 793482 |
| 10° | 388592 |
| 15° | 118934 |
| 20° | 50381 |
| 25° | 22792 |
| 30° | 8887 |
| 35° | 4096 |
| 40° | 1288 |
| 45° | 496 |
| 50° | 205 |
| 55° | 76 |
| 60° | 88 |
| 65° | 104 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 496 cd/sqm



TEST NUMBER: P1287932

CATALOG NUMBER: P3A05R15W2N902765DE010 E3D1WH_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 280.6 | 54.9 |
| 10°-20° | 172.2 | 33.7 |
| 20°-30° | 46.3 | 9.1 |
| 30°-40° | 10.2 | 2.0 |
| 40°-50° | 1.4 | 0.3 |
| 50°-60° | 0.3 | 0.1 |
| 60°-70° | 0.1 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 499.0 | 97.6 |
| 0°-40° | 509.2 | 99.6 |
| 0°-60° | 510.9 | 100.0 |
| 0°-90° | 511.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 511.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 4438 | |
| 5° | 3605 | 281 |
| 15° | 524 | 172 |
| 25° | 94 | 46 |
| 35° | 15 | 10 |
| 45° | 2 | 1 |
| 55° | 0 | 0 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1287932
CATALOG NUMBER: P3A05R15W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 4437.6 |
| 1° | 4409.9 |
| 2° | 4320.9 |
| 3° | 4160.7 |
| 4° | 3919.5 |
| 5° | 3604.8 |
| 6° | 3248.8 |
| 7° | 2852.4 |
| 8° | 2488.1 |
| 9° | 2102.0 |
| 10° | 1745.2 |
| 11° | 1392.2 |
| 12° | 1071.1 |
| 13° | 823.9 |
| 14° | 652.2 |
| 15° | 523.9 |
| 17.5° | 324.7 |
| 20° | 215.9 |
| 22.5° | 145.3 |
| 25° | 94.2 |
| 27.5° | 55.8 |
| 30° | 35.1 |
| 32.5° | 23.6 |
| 35° | 15.3 |
| 37.5° | 8.5 |
| 40° | 4.5 |
| 42.5° | 2.5 |
| 45° | 1.6 |
| 47.5° | 1.0 |
| 50° | 0.6 |
| 52.5° | 0.4 |
| 55° | 0.2 |
| 57.5° | 0.2 |
| 60° | 0.2 |
| 62.5° | 0.2 |
| 65° | 0.2 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |



TEST NUMBER: P1287932
CATALOG NUMBER: P3A05R15W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)