

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288068

Luminaire Tested: P3A05R15W2N902765DE010 E3PHLP1MW_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R15W2N902765DE010 E3PHLP1MW_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 6500K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 31.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288068
CATALOG NUMBER: P3A05R15W2N902765DE010 E3PHLP1MW_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1288068

CATALOG NUMBER: P3A05R15W2N902765DE010 E3PHLP1MW_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69622
5°	63922
10°	50923
15°	38071
20°	28913
25°	21896
30°	16205
35°	11564
40°	7929
45°	5551
50°	4708
55°	4626
60°	4780
65°	5085
70°	5193
75°	5338
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 6720 cd/sqm



TEST NUMBER: P1288068

CATALOG NUMBER: P3A05R15W2N902765DE010 E3PHLP1MW_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.7	13.8
10°-20°	47.0	25.3
20°-30°	41.7	22.4
30°-40°	27.3	14.7
40°-50°	14.6	7.8
50°-60°	11.0	5.9
60°-70°	9.5	5.1
70°-80°	6.5	3.5
80°-90°	2.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	114.4	61.5
0°-40°	141.7	76.2
0°-60°	167.3	90.0
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	318	
5°	290	26
15°	168	47
25°	90	42
35°	43	27
45°	18	15
55°	12	11
65°	10	9
75°	6	7
85°	2	3
90°	0	



TEST NUMBER: P1288068
CATALOG NUMBER: P3A05R15W2N902765DE010 E3PHLP1MW_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	317.5
2.5°	310.0
5°	290.4
7.5°	261.6
10°	228.7
12.5°	197.1
15°	167.7
17.5°	144.0
20°	123.9
22.5°	106.0
25°	90.5
27.5°	76.6
30°	64.0
32.5°	53.0
35°	43.2
37.5°	34.6
40°	27.7
42.5°	21.9
45°	17.9
47.5°	15.6
50°	13.8
52.5°	13.3
55°	12.1
57.5°	11.5
60°	10.9
62.5°	10.4
65°	9.8
67.5°	8.6
70°	8.1
72.5°	6.9
75°	6.3
77.5°	5.2
80°	4.6
82.5°	4.0
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)