

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288185

Luminaire Tested: P3A05R20W2N902750DE010 E3PH1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R20W2N902750DE010 E3PH1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288185

CATALOG NUMBER: P3A05R20W2N902750DE010 E3PH1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288185

CATALOG NUMBER: P3A05R20W2N902750DE010 E3PH1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	104	103	101	100	100	98	98	98	98	98	98	98	98	98	98	98	98
2	113	110	107	105	111	108	106	104	105	104	102	102	101	100	100	99	98	97	97	97	97	97	97	97	97	97	97	97	97
3	110	107	104	101	109	105	103	101	103	101	99	101	99	98	99	97	96	95	95	95	95	95	95	95	95	95	95	95	95
4	108	104	101	98	107	103	100	98	101	98	97	99	97	95	97	95	94	93	93	93	93	93	93	93	93	93	93	93	93
5	106	101	98	96	105	100	97	95	99	96	94	97	95	94	96	94	93	92	92	92	92	92	92	92	92	92	92	92	92
6	104	99	96	93	103	98	95	93	97	94	93	96	94	92	95	93	91	90	90	90	90	90	90	90	90	90	90	90	90
7	102	97	94	92	101	96	93	91	95	93	91	94	92	90	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88	88	88	88	88	88	88	88	88	88	88	88
9	99	94	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87	87	87	87	87	87	87	87	87	87	87	87
10	97	92	89	87	96	92	89	87	91	88	87	91	88	87	90	88	86	86	86	86	86	86	86	86	86	86	86	86	86

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	709899
5°	545255
10°	335910
15°	97753
20°	13044
25°	3871
30°	1165
35°	161
40°	172
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1288185

CATALOG NUMBER: P3A05R20W2N902750DE010 E3PH1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.3	57.8
10°-20°	140.7	39.4
20°-30°	9.1	2.5
30°-40°	0.9	0.3
40°-50°	0.1	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.1	99.7
0°-40°	357.0	100.0
0°-60°	357.0	100.0
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3237	
5°	2477	206
15°	431	141
25°	16	9
35°	1	1
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1288185

CATALOG NUMBER: P3A05R20W2N902750DE010 E3PH1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3237.4
2.5°	2919.1
5°	2477.1
7.5°	1987.2
10°	1508.6
12.5°	946.2
15°	430.6
17.5°	136.3
20°	55.9
22.5°	29.7
25°	16.0
27.5°	8.0
30°	4.6
32.5°	2.3
35°	0.6
37.5°	0.6
40°	0.6
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)