

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298719

Luminaire Tested: P3A13R65W2N902765DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298719
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R65W2N902765DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 341.0 lumens
Efficiency: N/A
Efficacy: 27.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298719

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1298719

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63		
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80410
5°	79463
10°	76440
15°	71601
20°	64406
25°	54681
30°	42766
35°	30490
40°	19952
45°	12342
50°	6277
55°	2217
60°	1930
65°	1920
70°	1731
75°	1694
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12342 cd/sqm

TEST NUMBER: P1298719

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.9	9.9
10°-20°	87.8	25.7
20°-30°	102.6	30.1
30°-40°	71.7	21.0
40°-50°	31.6	9.3
50°-60°	7.0	2.1
60°-70°	3.6	1.0
70°-80°	2.2	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	224.3	65.8
0°-40°	296.0	86.8
0°-60°	334.6	98.1
0°-90°	341.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	367	
5°	361	34
15°	315	88
25°	226	103
35°	114	72
45°	40	32
55°	6	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298719

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	366.7
2.5°	365.4
5°	361.0
7.5°	353.5
10°	343.3
12.5°	330.7
15°	315.4
17.5°	296.7
20°	276.0
22.5°	252.5
25°	226.0
27.5°	198.2
30°	168.9
32.5°	140.7
35°	113.9
37.5°	90.4
40°	69.7
42.5°	52.7
45°	39.8
47.5°	29.2
50°	18.4
52.5°	9.5
55°	5.8
57.5°	5.1
60°	4.4
62.5°	4.1
65°	3.7
67.5°	3.1
70°	2.7
72.5°	2.4
75°	2.0
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)