

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298720

Luminaire Tested: P3A13R65W2N902765DE010 E3DL1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1298720  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R65W2N902765DE010 E3DL1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 376.0 lumens  
Efficiency: N/A  
Efficacy: 30.6 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298720

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1298720

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     |  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  | 96  | 94  |  | 93  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  | 89  | 87  |  | 85  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 90  | 86  | 83  |  | 88  | 85  | 82  |  | 86  | 83  | 80  |  | 79  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  |  | 83  | 79  | 75  |  | 81  | 77  | 74  |  | 73  |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  |  | 77  | 73  | 70  |  | 76  | 72  | 69  |  | 68  |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 67  | 64  |  | 63  |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 64  | 61  |  | 69  | 64  | 60  |  | 67  | 63  | 60  |  | 58  |
| 8   | 77  | 67  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  |  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 55  |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  | 56  | 53  |  | 51  |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  |  | 58  | 53  | 50  |  | 57  | 53  | 49  |  | 48  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 88677 |
| 5°  | 87607 |
| 10° | 84278 |
| 15° | 78956 |
| 20° | 71010 |
| 25° | 60294 |
| 30° | 47172 |
| 35° | 33595 |
| 40° | 21984 |
| 45° | 13583 |
| 50° | 6891  |
| 55° | 2447  |
| 60° | 2149  |
| 65° | 2127  |
| 70° | 1923  |
| 75° | 1864  |
| 80° | 1894  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13583 cd/sqm

TEST NUMBER: P1298720

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 37.4   | 9.9       |
| 10°-20°   | 96.8   | 25.7      |
| 20°-30°   | 113.1  | 30.1      |
| 30°-40°   | 79.1   | 21.0      |
| 40°-50°   | 34.8   | 9.2       |
| 50°-60°   | 7.7    | 2.1       |
| 60°-70°   | 3.9    | 1.0       |
| 70°-80°   | 2.4    | 0.6       |
| 80°-90°   | 0.8    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 247.3  | 65.8      |
| 0°-40°    | 326.3  | 86.8      |
| 0°-60°    | 368.9  | 98.1      |
| 0°-90°    | 376.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 376.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 404 |      |
| 5°  | 398 | 37   |
| 15° | 348 | 97   |
| 25° | 249 | 113  |
| 35° | 126 | 79   |
| 45° | 44  | 35   |
| 55° | 6   | 8    |
| 65° | 4   | 4    |
| 75° | 2   | 2    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1298720

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DL1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 404.4 |
| 2.5°  | 402.9 |
| 5°    | 398.0 |
| 7.5°  | 389.8 |
| 10°   | 378.5 |
| 12.5° | 364.6 |
| 15°   | 347.8 |
| 17.5° | 327.2 |
| 20°   | 304.3 |
| 22.5° | 278.5 |
| 25°   | 249.2 |
| 27.5° | 218.5 |
| 30°   | 186.3 |
| 32.5° | 155.2 |
| 35°   | 125.5 |
| 37.5° | 99.7  |
| 40°   | 76.8  |
| 42.5° | 58.1  |
| 45°   | 43.8  |
| 47.5° | 32.2  |
| 50°   | 20.2  |
| 52.5° | 10.5  |
| 55°   | 6.4   |
| 57.5° | 5.6   |
| 60°   | 4.9   |
| 62.5° | 4.5   |
| 65°   | 4.1   |
| 67.5° | 3.4   |
| 70°   | 3.0   |
| 72.5° | 2.6   |
| 75°   | 2.2   |
| 77.5° | 1.9   |
| 80°   | 1.5   |
| 82.5° | 1.1   |
| 85°   | 0.7   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)