

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288254

Luminaire Tested: P3A05R20W2N902765DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R20W2N902765DE010 E3D1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288254

CATALOG NUMBER: P3A05R20W2N902765DE010 E3D1WH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288254

CATALOG NUMBER: P3A05R20W2N902765DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	99	99	99	99	99	99	99	99	99	99	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	96	96	96	96	96	96	96	96	96	96	96	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	94	94	94	94	94	94	94	94	94	94	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	92	92	92	92	92	92	92	92	92	92	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	90	90	90	90	90	90	90	90	90	90	90	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	88	88	88	88	88	88	88	88	88	88	88	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	86	86	86	86	86	86	86	86	86	86	86	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	84	84	84	84	84	84	84	84	84	84	84	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	82	82	82	82	82	82	82	82	82	82	82	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	81	81	81	81	81	81	81	81	81	81	81	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	752396
5°	633478
10°	395673
15°	147924
20°	50778
25°	21171
30°	9976
35°	4470
40°	2118
45°	1085
50°	409
55°	76
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1085 cd/sqm

TEST NUMBER: P1288254

CATALOG NUMBER: P3A05R20W2N902765DE010 E3D1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	239.3	48.2
10°-20°	197.1	39.7
20°-30°	44.8	9.0
30°-40°	11.4	2.3
40°-50°	2.9	0.6
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	481.3	97.0
0°-40°	492.7	99.3
0°-60°	495.9	100.0
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3431	
5°	2878	239
15°	652	197
25°	88	45
35°	17	11
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1288254

CATALOG NUMBER: P3A05R20W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3431.2
1°	3402.1
2°	3316.4
3°	3193.4
4°	3042.5
5°	2877.9
6°	2694.4
7°	2492.0
8°	2255.8
9°	2021.7
10°	1777.0
11°	1516.5
12°	1256.5
13°	1036.2
14°	825.6
15°	651.6
16°	514.3
17°	405.7
18°	326.0
19°	265.1
20°	217.6
21°	181.9
22°	151.8
23°	126.2
24°	105.3
25°	87.5
27.5°	57.2
30°	39.4
32.5°	24.2
35°	16.7
37.5°	10.7
40°	7.4
42.5°	5.0
45°	3.5
47.5°	2.3
50°	1.2
52.5°	0.6
55°	0.2
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1288254

CATALOG NUMBER: P3A05R20W2N902765DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)