

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288395

Luminaire Tested: P3A05R25W2N902750DE010 E3D1MW\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1288395  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A05R25W2N902750DE010 E3D1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,  
E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 456.0 lumens  
Efficiency: N/A  
Efficacy: 77.3 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288395

CATALOG NUMBER: P3A05R25W2N902750DE010 E3D1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1288395

CATALOG NUMBER: P3A05R25W2N902750DE010 E3D1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 99 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 103 | 102 | 100 | 99  | 99  | 97  | 96 | 96 |
| 2   | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  | 93 | 93 |
| 3   | 108 | 104 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  | 98  | 96  | 94  | 96  | 94  | 93  | 92  | 91 | 91 |
| 4   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 93  | 97  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 89  | 88 | 88 |
| 5   | 103 | 97  | 93  | 90  | 101 | 96  | 93  | 90  | 95  | 92  | 89  | 93  | 91  | 89  | 92  | 90  | 88  | 87  | 86 | 86 |
| 6   | 100 | 94  | 90  | 87  | 99  | 93  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 90  | 87  | 86  | 85  | 84 | 84 |
| 7   | 97  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 83  | 82 | 82 |
| 8   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 81  | 80 | 80 |
| 9   | 93  | 87  | 83  | 80  | 92  | 86  | 83  | 80  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  | 78 | 78 |
| 10  | 91  | 85  | 81  | 78  | 90  | 84  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 80  | 78  | 77  | 76 | 76 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 487527 |
| 5°  | 452167 |
| 10° | 350673 |
| 15° | 175824 |
| 20° | 57778  |
| 25° | 22961  |
| 30° | 8609   |
| 35° | 2490   |
| 40° | 1116   |
| 45° | 434    |
| 50° | 375    |
| 55° | 268    |
| 60° | 307    |
| 65° | 363    |
| 70° | 256    |
| 75° | 339    |
| 80° | 505    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 505 cd/sqm

TEST NUMBER: P1288395

CATALOG NUMBER: P3A05R25W2N902750DE010 E3D1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 180.7  | 39.6      |
| 10°-20°   | 215.6  | 47.3      |
| 20°-30°   | 48.6   | 10.7      |
| 30°-40°   | 7.9    | 1.7       |
| 40°-50°   | 1.4    | 0.3       |
| 50°-60°   | 0.8    | 0.2       |
| 60°-70°   | 0.7    | 0.1       |
| 70°-80°   | 0.4    | 0.1       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 444.8  | 97.5      |
| 0°-40°    | 452.7  | 99.3      |
| 0°-60°    | 454.9  | 99.8      |
| 0°-90°    | 456.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 456.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2223 |      |
| 5°  | 2054 | 181  |
| 15° | 774  | 216  |
| 25° | 95   | 49   |
| 35° | 9    | 8    |
| 45° | 1    | 1    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1288395

CATALOG NUMBER: P3A05R25W2N902750DE010 E3D1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2223.3 |
| 1°    | 2219.7 |
| 2°    | 2201.8 |
| 3°    | 2168.9 |
| 4°    | 2119.1 |
| 5°    | 2054.2 |
| 6°    | 1976.8 |
| 7°    | 1893.0 |
| 8°    | 1797.0 |
| 9°    | 1692.0 |
| 10°   | 1574.9 |
| 11°   | 1439.8 |
| 12°   | 1284.3 |
| 13°   | 1121.7 |
| 14°   | 947.2  |
| 15°   | 774.5  |
| 17.5° | 441.4  |
| 20°   | 247.6  |
| 22.5° | 149.4  |
| 25°   | 94.9   |
| 27.5° | 58.4   |
| 30°   | 34.0   |
| 32.5° | 17.9   |
| 35°   | 9.3    |
| 37.5° | 6.1    |
| 40°   | 3.9    |
| 42.5° | 2.5    |
| 45°   | 1.4    |
| 47.5° | 1.1    |
| 50°   | 1.1    |
| 52.5° | 1.1    |
| 55°   | 0.7    |
| 57.5° | 0.7    |
| 60°   | 0.7    |
| 62.5° | 0.7    |
| 65°   | 0.7    |
| 67.5° | 0.7    |
| 70°   | 0.4    |
| 72.5° | 0.4    |
| 75°   | 0.4    |
| 77.5° | 0.4    |
| 80°   | 0.4    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1288395

CATALOG NUMBER: P3A05R25W2N902750DE010 E3D1MW\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)