

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298756

Luminaire Tested: P3A13R65W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R65W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 295.0 lumens
Efficiency: N/A
Efficacy: 24.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298756

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298756

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52496
5°	51794
10°	50055
15°	47197
20°	43544
25°	39510
30°	34993
35°	29794
40°	23702
45°	16746
50°	9722
55°	5314
60°	4912
65°	4462
70°	4103
75°	3813
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16746 cd/sqm

TEST NUMBER: P1298756

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.1	7.5
10°-20°	58.2	19.7
20°-30°	74.8	25.3
30°-40°	69.2	23.4
40°-50°	41.8	14.2
50°-60°	14.3	4.8
60°-70°	8.6	2.9
70°-80°	4.8	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.1	52.6
0°-40°	224.2	76.0
0°-60°	280.2	95.0
0°-90°	295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	295.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	239	
5°	235	22
15°	208	58
25°	163	75
35°	111	69
45°	54	42
55°	14	14
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1298756

CATALOG NUMBER: P3A13R65W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	239.4
2.5°	238.3
5°	235.3
7.5°	230.8
10°	224.8
12.5°	217.3
15°	207.9
17.5°	197.8
20°	186.6
22.5°	175.0
25°	163.3
27.5°	151.0
30°	138.2
32.5°	125.5
35°	111.3
37.5°	97.4
40°	82.8
42.5°	68.2
45°	54.0
47.5°	40.8
50°	28.5
52.5°	18.0
55°	13.9
57.5°	12.4
60°	11.2
62.5°	9.7
65°	8.6
67.5°	7.5
70°	6.4
72.5°	5.6
75°	4.5
77.5°	3.7
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)