

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288426

Luminaire Tested: P3A05R25W2N902750DE010 E3DL1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288426
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R25W2N902750DE010 E3DL1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 414.1 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288426
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DL1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1288426

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DL1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97		95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92		90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87		86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83		82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79		78
6	94	86	81	78	92	86	81	77	84	80	77	83	79	76	82	78	76		75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73		72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70		69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67		66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	265571
5°	247765
10°	198482
15°	134734
20°	81534
25°	47664
30°	27143
35°	14937
40°	7929
45°	4186
50°	2422
55°	1797
60°	1579
65°	1660
70°	1539
75°	1356
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4186 cd/sqm



TEST NUMBER: P1288426

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DL1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	24.1
10°-20°	163.2	39.4
20°-30°	93.2	22.5
30°-40°	36.8	8.9
40°-50°	11.3	2.7
50°-60°	4.4	1.1
60°-70°	3.0	0.7
70°-80°	1.7	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	356.3	86.0
0°-40°	393.1	94.9
0°-60°	408.8	98.7
0°-90°	414.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1211	
5°	1126	100
15°	594	163
25°	197	93
35°	56	37
45°	14	11
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1288426

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1211.1
1°	1208.7
2°	1198.8
3°	1181.4
4°	1157.3
5°	1125.6
6°	1088.4
7°	1046.5
8°	997.8
9°	948.0
10°	891.4
11°	835.6
12°	774.3
13°	713.7
14°	651.6
15°	593.5
17.5°	460.1
20°	349.4
22.5°	262.3
25°	197.0
27.5°	146.0
30°	107.2
32.5°	77.5
35°	55.8
37.5°	39.6
40°	27.7
42.5°	19.0
45°	13.5
47.5°	9.5
50°	7.1
52.5°	5.5
55°	4.7
57.5°	4.4
60°	3.6
62.5°	3.2
65°	3.2
67.5°	2.8
70°	2.4
72.5°	2.0
75°	1.6
77.5°	1.2
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.4



TEST NUMBER: P1288426
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DL1MW_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)