

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288482

Luminaire Tested: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1288482  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRIS  
Catalog Number: P3A05R25W2N902750DE010 E3DLP1LI\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3500K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 257.0 lumens  
Efficiency: N/A  
Efficacy: 43.6 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1288482  
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1288482

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	93304
5°	89522
10°	78422
15°	63042
20°	48421
25°	36655
30°	26485
35°	17587
40°	10677
45°	6202
50°	3957
55°	3211
60°	2807
65°	2491
70°	2052
75°	2033
80°	1515
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6202 cd/sqm



TEST NUMBER: P1288482

CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	37.0	14.4
10°-20°	76.8	29.9
20°-30°	69.4	27.0
30°-40°	41.7	16.2
40°-50°	16.5	6.4
50°-60°	7.6	3.0
60°-70°	4.6	1.8
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.2	71.3
0°-40°	225.0	87.5
0°-60°	249.1	97.0
0°-90°	257.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	426	
5°	407	37
15°	278	77
25°	152	69
35°	66	42
45°	20	17
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1288482  
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	425.5
1°	425.5
2°	423.5
3°	419.1
4°	413.5
5°	406.7
6°	397.9
7°	387.8
8°	376.2
9°	364.6
10°	352.2
11°	337.8
12°	322.9
13°	308.1
14°	293.3
15°	277.7
17.5°	240.8
20°	207.5
22.5°	177.5
25°	151.5
27.5°	127.0
30°	104.6
32.5°	84.1
35°	65.7
37.5°	50.1
40°	37.3
42.5°	27.2
45°	20.0
47.5°	15.2
50°	11.6
52.5°	9.6
55°	8.4
57.5°	7.2
60°	6.4
62.5°	5.2
65°	4.8
67.5°	4.0
70°	3.2
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.2
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1288482  
CATALOG NUMBER: P3A05R25W2N902750DE010 E3DLP1LI\_3500K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)