

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288934

Luminaire Tested: P3A05R30W2N902765DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R30W2N902765DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 205.0 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288934

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288934

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90		
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86		
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82		
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78		
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75		
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71		
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69		
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	119618
5°	113867
10°	95768
15°	69058
20°	42844
25°	24364
30°	13521
35°	7362
40°	3893
45°	2109
50°	1126
55°	726
60°	658
65°	726
70°	641
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2109 cd/sqm

TEST NUMBER: P1288934

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	22.7
10°-20°	82.8	40.4
20°-30°	47.8	23.3
30°-40°	18.2	8.9
40°-50°	5.6	2.7
50°-60°	1.8	0.9
60°-70°	1.3	0.6
70°-80°	0.7	0.3
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.2	86.4
0°-40°	195.4	95.3
0°-60°	202.8	98.9
0°-90°	205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	205.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	546	
5°	517	47
15°	304	83
25°	101	48
35°	28	18
45°	7	6
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1288934

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	545.5
1°	545.1
2°	541.8
3°	535.7
4°	527.9
5°	517.3
6°	503.7
7°	488.6
8°	471.7
9°	451.6
10°	430.1
11°	406.9
12°	382.3
13°	356.5
14°	330.4
15°	304.2
17.5°	239.9
20°	183.6
22.5°	136.1
25°	100.7
27.5°	73.2
30°	53.4
32.5°	38.5
35°	27.5
37.5°	19.2
40°	13.6
42.5°	9.5
45°	6.8
47.5°	4.6
50°	3.3
52.5°	2.3
55°	1.9
57.5°	1.7
60°	1.5
62.5°	1.4
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.8
75°	0.6
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0



TEST NUMBER: P1288934

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)