

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1288970

Luminaire Tested: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1288970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R30W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 158.0 lumens
Efficiency: N/A
Efficacy: 26.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1288970

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1288970

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96	94	93		91
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89	87	85		83
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84	80	78		76
4	94	86	79	74	92	84	79	74	82	77	73		80	76	72		78	74	71		70
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73	69	66		64
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69	64	61		59
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65	60	57		55
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61	56	53		51
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49		48
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54	50	46		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37322
5°	36496
10°	33934
15°	30193
20°	25972
25°	21993
30°	18256
35°	14322
40°	10276
45°	6729
50°	3821
55°	2523
60°	2368
65°	2231
70°	1988
75°	1779
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6729 cd/sqm

TEST NUMBER: P1288970

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.4	9.7
10°-20°	37.0	23.4
20°-30°	41.7	26.4
30°-40°	33.3	21.1
40°-50°	17.1	10.8
50°-60°	6.4	4.1
60°-70°	4.2	2.7
70°-80°	2.3	1.4
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.0	59.5
0°-40°	127.3	80.6
0°-60°	150.8	95.5
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	170	
5°	166	15
15°	133	37
25°	91	42
35°	54	33
45°	22	17
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1288970

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	170.2
1°	170.2
2°	169.6
3°	168.7
4°	167.3
5°	165.8
6°	163.8
7°	161.3
8°	158.6
9°	155.5
10°	152.4
11°	148.9
12°	145.2
13°	141.3
14°	137.3
15°	133.0
17.5°	122.1
20°	111.3
22.5°	100.8
25°	90.9
27.5°	81.2
30°	72.1
32.5°	62.8
35°	53.5
37.5°	44.4
40°	35.9
42.5°	28.3
45°	21.7
47.5°	16.1
50°	11.2
52.5°	7.9
55°	6.6
57.5°	6.0
60°	5.4
62.5°	4.8
65°	4.3
67.5°	3.7
70°	3.1
72.5°	2.5
75°	2.1
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2



TEST NUMBER: P1288970

CATALOG NUMBER: P3A05R30W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)