

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299201

Luminaire Tested: P3A17R15W2N902750DE010 E3DLD1LI\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1299201  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R15W2N902750DE010 E3DLD1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 951.0 lumens  
Efficiency: N/A  
Efficacy: 49.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299201

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1LI\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299201

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 95  | 91  | 95  | 92  | 89  |  | 92  | 90  | 87  |  | 90  |
| 3   | 100 | 93  | 87  | 83  | 98  | 91  | 86  | 82  | 89  | 84  | 81  |  | 86  | 82  | 79  |  | 84  |
| 4   | 94  | 86  | 80  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 78  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  |  | 75  | 71  | 67  |  | 74  |
| 6   | 84  | 74  | 68  | 63  | 83  | 73  | 67  | 63  | 72  | 66  | 62  |  | 70  | 66  | 62  |  | 69  |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 63  | 58  | 67  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 8   | 76  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  |  | 59  | 54  | 50  |  | 58  |
| 10  | 68  | 58  | 52  | 48  | 67  | 57  | 51  | 47  | 57  | 51  | 47  |  | 56  | 51  | 47  |  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 239871 |
| 5°  | 233369 |
| 10° | 213267 |
| 15° | 186812 |
| 20° | 160244 |
| 25° | 133798 |
| 30° | 107080 |
| 35° | 80308  |
| 40° | 58281  |
| 45° | 38112  |
| 50° | 23846  |
| 55° | 16133  |
| 60° | 14253  |
| 65° | 13127  |
| 70° | 12374  |
| 75° | 11268  |
| 80° | 10607  |
| 85° | 9057   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38112 cd/sqm

TEST NUMBER: P1299201

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1LI\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 97.8   | 10.3      |
| 10°-20°   | 229.3  | 24.1      |
| 20°-30°   | 252.6  | 26.6      |
| 30°-40°   | 189.2  | 19.9      |
| 40°-50°   | 98.1   | 10.3      |
| 50°-60°   | 40.6   | 4.3       |
| 60°-70°   | 25.2   | 2.6       |
| 70°-80°   | 14.1   | 1.5       |
| 80°-90°   | 4.1    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 579.7  | 61.0      |
| 0°-40°    | 768.9  | 80.9      |
| 0°-60°    | 907.6  | 95.4      |
| 0°-90°    | 951.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 951.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1094 |      |
| 5°  | 1060 | 98   |
| 15° | 823  | 229  |
| 25° | 553  | 253  |
| 35° | 300  | 189  |
| 45° | 123  | 98   |
| 55° | 42   | 41   |
| 65° | 25   | 25   |
| 75° | 13   | 14   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1299201

CATALOG NUMBER: P3A17R15W2N902750DE010 E3DLD1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1093.9 |
| 1°    | 1095.1 |
| 2°    | 1091.5 |
| 3°    | 1084.3 |
| 4°    | 1073.4 |
| 5°    | 1060.2 |
| 6°    | 1043.3 |
| 7°    | 1025.3 |
| 8°    | 1003.6 |
| 9°    | 980.7  |
| 10°   | 957.8  |
| 12.5° | 891.5  |
| 15°   | 822.9  |
| 17.5° | 754.2  |
| 20°   | 686.7  |
| 22.5° | 618.0  |
| 25°   | 553.0  |
| 27.5° | 487.9  |
| 30°   | 422.9  |
| 32.5° | 359.0  |
| 35°   | 300.0  |
| 37.5° | 249.4  |
| 40°   | 203.6  |
| 42.5° | 161.4  |
| 45°   | 122.9  |
| 47.5° | 92.8   |
| 50°   | 69.9   |
| 52.5° | 51.8   |
| 55°   | 42.2   |
| 57.5° | 37.3   |
| 60°   | 32.5   |
| 62.5° | 28.9   |
| 65°   | 25.3   |
| 67.5° | 21.7   |
| 70°   | 19.3   |
| 72.5° | 15.7   |
| 75°   | 13.3   |
| 77.5° | 10.8   |
| 80°   | 8.4    |
| 82.5° | 6.0    |
| 85°   | 3.6    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)