

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299261

Luminaire Tested: P3A17R15W2N902750DE010 E3PHLP1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R15W2N902750DE010 E3PHLP1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 562.1 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299261
CATALOG NUMBER: P3A17R15W2N902750DE010 E3PHLP1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299261

CATALOG NUMBER: P3A17R15W2N902750DE010 E3PHLP1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	13.8
10°-20°	142.1	25.3
20°-30°	125.9	22.4
30°-40°	82.5	14.7
40°-50°	44.1	7.8
50°-60°	33.3	5.9
60°-70°	28.7	5.1
70°-80°	19.8	3.5
80°-90°	8.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	345.7	61.5
0°-40°	428.1	76.2
0°-60°	505.5	89.9
0°-90°	562.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	562.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	959	
5°	877	78
15°	507	142
25°	273	126
35°	131	82
45°	54	44
55°	37	33
65°	30	29
75°	19	20
85°	7	8
90°	0	



TEST NUMBER: P1299261
CATALOG NUMBER: P3A17R15W2N902750DE010 E3PHLP1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	959.3
2.5°	936.6
5°	877.4
7.5°	790.4
10°	691.2
12.5°	595.4
15°	506.6
17.5°	435.2
20°	374.3
22.5°	320.3
25°	273.3
27.5°	231.5
30°	193.2
32.5°	160.2
35°	130.6
37.5°	104.5
40°	83.6
42.5°	66.2
45°	54.0
47.5°	47.0
50°	41.8
52.5°	40.0
55°	36.6
57.5°	34.8
60°	33.1
62.5°	31.3
65°	29.6
67.5°	26.1
70°	24.4
72.5°	20.9
75°	19.2
77.5°	15.7
80°	13.9
82.5°	12.2
85°	7.0
87.5°	3.5
90°	0.0

(END OF REPORT)