

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299323

Luminaire Tested: P3A17R15W2N902765DE010 E3D1WMH\_3000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1299323  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R15W2N902765DE010 E3D1WMH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1544.0 lumens  
Efficiency: N/A  
Efficacy: 79.6 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299323

CATALOG NUMBER: P3A17R15W2N902765DE010 E3D1WMH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299323

CATALOG NUMBER: P3A17R15W2N902765DE010 E3D1WMH\_3000K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 116 | 114 | 112 | 111 |  | 113 | 112 | 110 | 109 |  | 108 | 107 | 105 |  | 104 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |  |  |   |
| 2   | 112 | 109 | 107 | 105 |  | 110 | 108 | 105 | 103 |  | 105 | 103 | 101 |  | 102 | 100 | 99  |  | 99  | 98  | 97  |  | 96  |  |  |   |
| 3   | 110 | 106 | 102 | 100 |  | 108 | 104 | 102 | 99  |  | 102 | 100 | 98  |  | 100 | 98  | 96  |  | 98  | 96  | 95  |  | 94  |  |  |   |
| 4   | 107 | 102 | 99  | 96  |  | 105 | 101 | 98  | 96  |  | 99  | 97  | 95  |  | 98  | 96  | 94  |  | 96  | 94  | 93  |  | 92  |  |  |   |
| 5   | 105 | 100 | 96  | 94  |  | 103 | 99  | 96  | 93  |  | 97  | 94  | 92  |  | 96  | 93  | 92  |  | 94  | 93  | 91  |  | 90  |  |  |   |
| 6   | 102 | 97  | 94  | 91  |  | 101 | 96  | 93  | 91  |  | 95  | 92  | 90  |  | 94  | 92  | 90  |  | 93  | 91  | 89  |  | 88  |  |  |   |
| 7   | 100 | 95  | 91  | 89  |  | 99  | 94  | 91  | 89  |  | 93  | 90  | 88  |  | 92  | 90  | 88  |  | 91  | 89  | 88  |  | 87  |  |  |   |
| 8   | 98  | 93  | 89  | 87  |  | 97  | 92  | 89  | 87  |  | 91  | 89  | 87  |  | 91  | 88  | 86  |  | 90  | 88  | 86  |  | 85  |  |  |   |
| 9   | 96  | 91  | 88  | 85  |  | 96  | 91  | 87  | 85  |  | 90  | 87  | 85  |  | 89  | 87  | 85  |  | 88  | 86  | 85  |  | 84  |  |  |   |
| 10  | 95  | 89  | 86  | 84  |  | 94  | 89  | 86  | 84  |  | 88  | 85  | 83  |  | 88  | 85  | 83  |  | 87  | 85  | 83  |  | 82  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 2940181 |
| 5°  | 2397528 |
| 10° | 1174171 |
| 15° | 359389  |
| 20° | 152193  |
| 25° | 68835   |
| 30° | 26840   |
| 35° | 12394   |
| 40° | 3864    |
| 45° | 1458    |
| 50° | 614     |
| 55° | 229     |
| 60° | 263     |
| 65° | 311     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 1458 cd/sqm

TEST NUMBER: P1299323

CATALOG NUMBER: P3A17R15W2N902765DE010 E3D1WMH\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 847.8  | 54.9      |
| 10°-20°   | 520.2  | 33.7      |
| 20°-30°   | 139.7  | 9.0       |
| 30°-40°   | 30.8   | 2.0       |
| 40°-50°   | 4.3    | 0.3       |
| 50°-60°   | 0.8    | 0.1       |
| 60°-70°   | 0.4    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1507.8 | 97.7      |
| 0°-40°    | 1538.6 | 99.6      |
| 0°-60°    | 1543.7 | 100.0     |
| 0°-90°    | 1544.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1544.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 13408 |      |
| 5°  | 10892 | 848  |
| 15° | 1583  | 520  |
| 25° | 284   | 140  |
| 35° | 46    | 31   |
| 45° | 5     | 4    |
| 55° | 1     | 1    |
| 65° | 1     | 0    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |

TEST NUMBER: P1299323

CATALOG NUMBER: P3A17R15W2N902765DE010 E3D1WMH\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |         |
|-------|---------|
| 0°    | 13408.3 |
| 1°    | 13324.5 |
| 2°    | 13055.8 |
| 3°    | 12571.6 |
| 4°    | 11842.7 |
| 5°    | 10892.0 |
| 6°    | 9816.5  |
| 7°    | 8618.6  |
| 8°    | 7517.9  |
| 9°    | 6351.1  |
| 10°   | 5273.3  |
| 11°   | 4206.6  |
| 12°   | 3236.4  |
| 13°   | 2489.4  |
| 14°   | 1970.7  |
| 15°   | 1583.1  |
| 17.5° | 981.2   |
| 20°   | 652.2   |
| 22.5° | 439.1   |
| 25°   | 284.5   |
| 27.5° | 168.6   |
| 30°   | 106.0   |
| 32.5° | 71.4    |
| 35°   | 46.3    |
| 37.5° | 25.8    |
| 40°   | 13.5    |
| 42.5° | 7.6     |
| 45°   | 4.7     |
| 47.5° | 2.9     |
| 50°   | 1.8     |
| 52.5° | 1.2     |
| 55°   | 0.6     |
| 57.5° | 0.6     |
| 60°   | 0.6     |
| 62.5° | 0.6     |
| 65°   | 0.6     |
| 67.5° | 0.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |



TEST NUMBER: P1299323

CATALOG NUMBER: P3A17R15W2N902765DE010 E3D1WMH\_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)