

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299394

Luminaire Tested: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299394  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 2700K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 854.0 lumens  
Efficiency: N/A  
Efficacy: 44.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 19.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299394  
CATALOG NUMBER: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299394

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65	65	65	65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56	56	56	56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	215399
5°	209575
10°	191513
15°	167742
20°	143909
25°	120152
30°	96141
35°	72116
40°	52327
45°	34236
50°	21389
55°	14489
60°	12806
65°	11778
70°	11092
75°	10082
80°	9597
85°	8051

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34236 cd/sqm



TEST NUMBER: P1299394

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.9	10.3
10°-20°	205.9	24.1
20°-30°	226.9	26.6
30°-40°	169.9	19.9
40°-50°	88.1	10.3
50°-60°	36.5	4.3
60°-70°	22.6	2.6
70°-80°	12.7	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.6	61.0
0°-40°	690.5	80.9
0°-60°	815.0	95.4
0°-90°	854.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	854.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	982	
5°	952	88
15°	739	206
25°	497	227
35°	269	170
45°	110	88
55°	38	36
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1299394

CATALOG NUMBER: P3A17R15W2N902765DE010 E3DLD1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	982.3
1°	983.4
2°	980.2
3°	973.7
4°	964.0
5°	952.1
6°	936.9
7°	920.7
8°	901.2
9°	880.7
10°	860.1
12.5°	800.6
15°	738.9
17.5°	677.3
20°	616.7
22.5°	555.0
25°	496.6
27.5°	438.2
30°	379.7
32.5°	322.4
35°	269.4
37.5°	223.9
40°	182.8
42.5°	145.0
45°	110.4
47.5°	83.3
50°	62.7
52.5°	46.5
55°	37.9
57.5°	33.5
60°	29.2
62.5°	26.0
65°	22.7
67.5°	19.5
70°	17.3
72.5°	14.1
75°	11.9
77.5°	9.7
80°	7.6
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

(END OF REPORT)