

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299455

Luminaire Tested: P3A17R20W2N902750DE010 E3CB1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1299455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R20W2N902750DE010 E3CB1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1508.0 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1299455

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CB1MB_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1299455

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CB1MB_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	116	114	112	110		113	112	110	109		108	106	105		104	103	102		101	100	99		98			
2	112	109	107	104		110	108	105	103		104	103	101		102	100	99		99	98	97		95			
3	109	105	102	100		108	104	101	99		102	99	97		99	98	96		97	96	95		93			
4	107	102	99	96		105	101	98	96		99	97	95		97	95	93		96	94	92		91			
5	104	99	96	93		103	98	95	93		97	94	92		95	93	91		94	92	91		90			
6	102	97	93	91		101	96	93	90		95	92	90		94	91	89		93	90	89		88			
7	100	94	91	88		99	94	91	88		93	90	88		92	89	87		91	89	87		86			
8	98	92	89	86		97	92	89	86		91	88	86		90	88	86		89	87	85		85			
9	96	90	87	85		95	90	87	85		89	86	84		89	86	84		88	86	84		83			
10	94	89	85	83		93	88	85	83		88	85	83		87	84	83		86	84	82		82			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2342093
5°	2032858
10°	1256089
15°	436279
20°	133968
25°	47374
30°	17522
35°	7040
40°	3750
45°	1489
50°	819
55°	918
60°	1053
65°	623
70°	769
75°	1017
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1489 cd/sqm

TEST NUMBER: P1299455

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CB1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	766.5	50.8
10°-20°	608.1	40.3
20°-30°	105.3	7.0
30°-40°	19.1	1.3
40°-50°	4.4	0.3
50°-60°	2.2	0.1
60°-70°	1.3	0.1
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1479.9	98.1
0°-40°	1499.0	99.4
0°-60°	1505.6	99.8
0°-90°	1508.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1508.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10681	
5°	9235	766
15°	1922	608
25°	196	105
35°	26	19
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1299455

CATALOG NUMBER: P3A17R20W2N902750DE010 E3CB1MB_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	10680.8
1°	10629.5
2°	10426.6
3°	10100.7
4°	9718.7
5°	9235.3
6°	8681.4
7°	8036.9
8°	7302.8
9°	6478.0
10°	5641.2
12.5°	3558.3
15°	1921.8
17.5°	1026.5
20°	574.1
22.5°	328.3
25°	195.8
27.5°	119.4
30°	69.2
32.5°	40.6
35°	26.3
37.5°	17.9
40°	13.1
42.5°	8.4
45°	4.8
47.5°	2.4
50°	2.4
52.5°	2.4
55°	2.4
57.5°	2.4
60°	2.4
62.5°	1.2
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)